

DeWalt DCD716D2K-B1

12V 10MM Hammer Drill Driver 2.0Ah x2

Introduction

The **DCD716D2K-B1 10.8V/12V MAX* Cordless Sub-Compact Hammer Drill/Driver Kit** is an ultra-lightweight, ergonomic solution built for efficient drilling and fastening in confined spaces. Driven by a dependable fan-cooled motor producing up to 30 Nm of torque, it features a 2-speed transmission and 15 adjustable torque settings for accurate control across varied materials. Equipped with a dedicated percussion hammer function delivering up to 22,500 BPM, a 10mm keyless chuck, and a bright built-in LED work light, it smoothly handles masonry, wood, and metal applications. This complete kit includes two 2.0Ah batteries, a charger, and a heavy-duty carry case, making it perfect for light installations, repairs, and assembly work.

Key Features

- **Maximum Torque:** Up to 1925 Nm for the toughest jobs.
- **Brushless Motor:** Superior power and longevity.
- **3/4" Hog Ring Anvil:** Quick socket changes.
- **Variable Speed Trigger:** Enhanced control.
- **LED Work Light:** Better visibility.
- **TSTAK Case:** Secure storage and transport.

Specifications Table

Specification	Details
Voltage	10.8 / 12V
Battery chemistry	Li-Ion
Battery capacity	2.0 Ah
Battery	2
Charger	Yes
Power output	180 W
Speed settings	2
No load speed 1st gear	0 - 400 min-1
No load speed 2nd gear	0 - 1500 min-1
Impact rate 1st gear	0 - 6000 min-1
Impact rate 2nd gear	0 - 22500 min-1
Torque Setting	15
Max torque	30 Nm
Chuck capacity	10 mm
Chuck type	Plastic (Keyless)