

PRODUCT-DETAILS

TA42DU-32

TA42DU-32 Thermal Overload Relay 22 ... 32 A



General Information	
Extended Product Type	TA42DU-32
Product ID	1SAZ311201R1002
EAN	4013614216664
Catalog Description	TA42DU-32 Thermal Overload Relay 22 32 A
Long Description	The TA42DU-32 thermal overload relay is an economic electromechanical protection device for the main circuit. It offers reliable and fast protection for motors in the event of overload or phase failure. The device has trip class 10A. Further features are the temperature compensation, trip contact (NC), signal contact (NO), automatic- or manual reset selectable, trip-free mechanism, STOP- and Test function and a trip indication. The overload relays are connected directly to the block contactors. Single

Ordering	
Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Popular Downloads	
Instructions and Manuals	2CDC106049M6802
Instructions and	1SAC200017M0002

Manua	de 1	Dart	21

Time-Current Characteristic Curve	1SAZ300501F0002
Dimension Diagram	1SAZ300401F0001

Dimensions	
Product Net Width	54 mm
Product Net Height	90 mm
Product Net Depth / Length	111 mm
Product Net Weight	0.335 kg

Technical	
Setting Range	22 32 A
Rated Operational Voltage	Auxiliary Circuit 440 V DC Auxiliary Circuit 500 V AC Main Circuit 690 V AC Main Circuit 440 V DC
Rated Operational Current (I _e)	32 A
Rated Frequency (f)	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Auxiliary Circuit DC Main Circuit 60 Hz Main Circuit 50 Hz Main Circuit DC
Rated Impulse Withstand Voltage (U _{imp})	Auxiliary Circuit 6 kV Main Circuit 6 kV
Rated Insulation Voltage (U _i)	690 V
Number of Poles	3
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	1
Number of Protected Poles	3
Conventional Free-air Thermal Current (I _{th})	Auxiliary Circuit NC 10 A Auxiliary Circuit NO 6 A
Rated Operational Current AC-15 (I _e)	(120 V) NC 3 A (120 V) NO 1.5 A (240 V) NC 3 A (240 V) NO 1.5 A (400 V) NC 1.9 A (400 V) NO 1 A (440 V) NC 1 (500 V) NC 1 (500 V) NC 1
Rated Operational Current DC-13 (I _e)	(125 V) NC 0.25 A (125 V) NO 0.25 A (24 V) NC 1.25 A (24 V) NO 1.25 A (250 V) NC 0.12 A (250 V) NO 0.04 A (60 V) NC 0.25 A (60 V) NO 0.25 A
Degree of Protection	Housing IP20 Main Circuit Terminals IP10

TA42DU-32 3

Pollution Degree	3
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 2.5 mm² Flexible 1/2x 0.75 2.5 mm² Rigid 1/2x 0.75 4 mm²
Connecting Capacity Main Circuit	Flexible with Ferrule 1x 2.5 25 mm² Flexible with Ferrule 2x 2.5 10 mm² Rigid 1x 2.5 25 mm² Rigid 2x 2.5 16 mm²
Tightening Torque	Auxiliary Circuit 1 1.3 N·m Main Circuit 4.5 N·m
Wire Stripping Length	Auxiliary Circuit 9 mm Main Circuit 14 mm
Recommended Screw Driver	Auxiliary Circuit Pozidriv 1 Main Circuit Pozidriv 2
Power Loss	at Rated Operating Conditions per Pole 1.4 3.0 W
Suitable For	A30 A40 AL30 AL40
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1

Technical UL/CSA	
Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Contact Rating UL/CSA	(NC:) B600 (NO:) C300
Connecting Capacity Main Circuit UL/CSA	Flexible 1/2x 8-1 AWG Stranded 1/2x 8-1 AWG
Connecting Capacity Auxiliary Circuit UL/CSA	Flexible 1/2x 18-14 AWG Stranded 1/2x 18-14 AWG
Tightening Torque UL/CSA	Auxiliary Circuit 12 in·lb Main Circuit 40 in·lb

Environmental	
Ambient Air Temperature	Operation -25 +55 °C Operation Compensated -25 +55 °C Storage -40 +70 °C
Ambient Air Temperature Compensation	Yes
Maximum Operating Altitude Permissible	2000 m
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 12g 25g 2 shocks 13 ms
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Certificates and Declarations	
ABS Certificate	1SAA941000-0102
BV Certificate	1SAA941000-0201
CB Certificate	1SAA941017-2001
CQC Certificate	CQC2016010309922938
Declaration of	2020980304001323

TA42DU-32 4

Conformity - CCC	
Declaration of	1SAD101100-3509
Conformity - CE	
Declaration of	1SAD201100-3509
Conformity - UKCA	
DNV Certificate	1SAA941000-0304
DNV GL Certificate	1SAA941000-0304
EAC Certificate	1SAA941002-2702
GL Certificate	1SAA941000-0304
LR Certificate	1SAA941000-0504
RMRS Certificate	1SAA941000-0704
UL Certificate	E48139-19970506

Container Information	
Package Level 1 Units	1 piece
Package Level 1 Width	92 mm
Package Level 1 Height	109 mm
Package Level 1 Depth / Length	61 mm
Package Level 1 Gross Weight	0.36 kg
Package Level 1 EAN	4013614216664
Package Level 2 Units	24 piece
Package Level 2 Width	280 mm
Package Level 2 Height	210 mm
Package Level 2 Depth / Length	395 mm
Package Level 2 Gross Weight	8.786 kg
Package Level 2 EAN	4013614493737

Classifications	
Object Classification	F
Code	
ETIM 4	EC000106 - Thermal overload relay
ETIM 5	EC000106 - Thermal overload relay
ETIM 6	EC000106 - Thermal overload relay
ETIM 7	EC000106 - Thermal overload relay
ETIM 8	EC000106 - Thermal overload relay
eClass	V11.0 : 27371501
UNSPSC	39122330
IDEA Granular Category	5366 >> Thermal overload relay
Code (IGCC)	
E-Number (Finland)	3709382

TA42DU-32 5

Categories

 $Low\ Voltage\ Products\ and\ Systems \rightarrow Control\ Products \rightarrow Contactors \rightarrow Thermal\ Overload\ Relays$

