



ENGLISH

Datasheet

Stock No: 386-089

RS Pro Steel Alloy Compression, Extension Spring Kit, 342 Springs



Product Details

Miniature Spring Kit

342 pre-galvanised music wire springs

Supplied in plastic compartment box with spring sizes and box layout information.

Dimensions			
Type	Size (mm)	Qty.	Wire Dia. (mm)
Extension	L. 6.35 to 27.2	6 x 30 sizes	0.18 to 0.36
	D. 1.6 to 4		
Compression	L. 3.18 to 19.05	6 x 27 sizes	0.15 to 0.25
	D. 1.45 to 2.75		



ENGLISH

Specifications:

Material	Steel Alloy
Spring Types	Compression, Extension
Spring Quantity	342
Maximum Length	19.05 mm, 27.2 mm
Minimum Diameter	1.45 mm, 1.6 mm
Minimum Length	3.18 mm, 6.35 mm



GB WD = Wire diameter
 OD = Outside diameter
 FL = Free length

D WD = Drahtstärke
 OD = Außendurchmesser
 FL = Länge

I WD = Diametro filo
 OD = Diametro esterno
 FL = Lunghezza libera

Dimensions Abmessungen Dimensioni				Dimensions Abmessungen Dimensioni				Dimensions Abmessungen Dimensioni				Dimensions Abmessungen Dimensioni				Dimensions Abmessungen Dimensioni				Dimensions Abmessungen Dimensioni			
RS	WD	OD	FL	RS	WD	OD	FL	RS	WD	OD	FL	RS	WD	OD	FL	RS	WD	OD	FL	RS	WD	OD	FL
386-354	0.15	1.45	3.18	386-382	0.18	1.45	3.18	386-411	0.2	1.20	7.8	386-455	0.2	1.45	12.7	386-483	0.2	2.24	3.18	386-512	0.2	2.70	12.40
386-360	0.15	1.45	7.95	386-398	0.18	1.45	7.95	386-427	0.2	1.40	9.3	386-461	0.2	1.80	13.3	386-499	0.2	2.24	7.98	386-528	0.25	1.45	3.30
386-376	0.15	1.45	12.70	386-405	0.18	1.45	12.70	386-433	0.2	1.45	3.18	386-477	0.2	2.20	12.6	386-506	0.2	2.24	12.7	386-534	0.25	1.45	9.40
386-556	0.25	1.85	12.5	386-590	0.25	2.24	19.05	386-629	0.25	2.26	12.5	386-095	0.18	1.6	6.35	386-124	0.2	1.6	6.35	386-152	0.23	1.6	6.35
386-562	0.25	2.24	3.18	386-607	0.25	2.26	3.5	386-635	0.25	2.26	19.0	386-102	0.18	1.6	9.35	386-130	0.2	1.6	12.7	386-168	0.23	1.6	12.7
386-578	0.25	2.24	7.95	386-613	0.25	2.26	9.5	408-511	0.25	2.75	15.7	386-118	0.18	1.6	12.70	386-146	0.2	1.6	19.05	386-174	0.23	1.6	19.05
386-584	0.25	2.24	12.7																				
386-180	0.25	2.2	16.4	386-219	0.25	2.5	12.5	386-247	0.25	2.75	23.3	386-275	0.32	2.82	23.7	386-304	0.33	2.39	25.40	386-332	0.36	2.39	19.05
386-196	0.25	2.39	12.7	386-225	0.25	2.5	25.0	386-253	0.28	2.39	11.10	386-281	0.32	3.52	20.0	386-310	0.36	2.39	9.53	386-348	0.36	2.5	24.8
386-203	0.25	2.39	25.4	386-231	0.25	2.75	10.0	386-269	0.28	2.39	25.4	386-297	0.33	2.39	12.7	386-326	0.36	2.39	12.70	408-505	0.36	4.0	27.2