# KP (FH)

#### IEC Appliance Inlet C14 with Fuseholder 1- or 2-pole





Medical fuse drawer

Inlet with fuseholder (5x20 mm)

KPF Filter Module (not enclosed)







- Panel Mount: Sandwich/rear-side

- 2 Functions:

Appliance Inlet Protection class I, Fuseholder for fuse-links 5 x 20 mm 1- or 2-pole

- For PCB mounting

#### **Approvals**

- Approval Reference Type: KP01 - VDE Certificate Number: 40029370

- UL File Number: E93617 - CSA File Number: 38456

- CCC File Number: 2013010204594658













#### **Characteristics**

- Panel mount from rear or "sandwich" between top and bottom/side to side panels
  - PCB mount with snap-in or screw-on feet (self tapping screws Ø 3 x 8
- All single elements are already wired
- Fuse drawer meets requirements of medical standard IEC/EN 60601-1
- Insulation cover on the rear-side
- Suitable for use in equipment according to IEC/UL 60950

### Other versions on request

- Solder terminals
- Quick-connect terminals
- For protection class II

### References

Alternative: version with line filter KPF

#### Weblinks

pdf-datasheet, html-datasheet, General Product Information, Approvals, CE declaration of conformity, RoHS, CHINA-RoHS, REACH, Mating Connectors, e-Shop, SCHURTER-Stock-Check, Distributor-Stock-Check, CAD-Drawings, Accessories, Detailed request for product

Newly available variants corresponding to V-Lock mating cordset. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.


### **Technical Data**

Ratings IEC	10A / 250VAC; 50Hz
Ratings UL/CSA	10A / 125 VAC; 60 Hz
Dielectric Strength	> 2.3 kVAC between L-N
	> 2.8 kVAC between L/N-PE
	(1 min/50 Hz)
Allowable Operation Temp.	-25 °C to 70 °C
Degree of Protection	from front side IP 40 acc. to IEC 60529
Protection Class	Suitable for appliances with protection
	class I acc. to IEC 61140
Terminal	For PCB mounting Quick connect termi-
	nals 4.8 x 0.8 mm
	Solder terminal on request
Panel Thickness s	Snap-in: 1.5/2/2.5/3 mm
Material: Housing	Thermoplastic, black, UL 94V-0


C14 acc. to IEC 60320,
UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10 A, Protection Class I
1 or 2 pole, Shocksafe category PC2 acc. to IEC 60127-6, for fuse-links 5 x 20mm
5 x 20: 2W (1 pole)/ 1.6W (2-pole) per pole
Admissible power acceptance at higher ambient temperature see derating curves

### **Dimensions**

Screw-on mounting




 $\label{eq:A} A = \text{for PCB-thickness 1.2/1.6/2.0/2.4 mm} \\ \text{Additional quick connect terminal 4.8 x 0.8 mm} \\ \text{Snap-in mounting}$ 




Additional quick connect terminal 4.8 x 0.8 mm  $s = panel \ thickness$ 



For 2-pole inlet/switch, 2-pole inlet fuseholder and inlet/outlet



oFr combinations: Inlet/switch 1-pole, inlet/fuseholder 1-pole



 $d1 = 6 \pm 0.05$  für (snap-in)

d1 = 3.6 (screw-on)


d2 = 2.1 + 0.1/-0 (screw-on)


Dimensions without tolerance:

 $\leq 15 = \pm 0.05; \geq 15 = \pm 0.1$ 

Mounting holes for backside mounting








X = 48.4 at S = 1.5 and 2.5 X = 50.4 at S = 2.0 and 3.0

Sandwich mounting holes


S and X see mounting holes




X = 48.4 at S = 1.5 and 2.5 X = 50.4 at S = 2.0 and 3.0

## **Assembly Instructions**


52.4 ±0.1




Stable snap feet requires minimal insertion force




Module must lay flat on the PCB when soldering








Insertion from behind




"Sandwich" mounting with split enclosure panels


### **Diagrams**



# (5 x 20 mm)

# **Derating Curves**







### **All Variants**

Panel mounting	Panel Thickness s [mm]	PCB [mm]	Line Switch	Fuseholder	Connector	Order Number
Snap-in	2	1.6	-	1-pole	-	KP01.1412.01
Snap-in	2	1.6	-	2-pole	-	KP01.1312.01
Snap-in	3	1.6	-	1-pole	-	KP01.1413.01
Snap-in	3	1.6	-	2-pole	-	KP01.1313.01
Screw	2	1.2/1.6/2.0/2.4	-	1-pole	-	KP01.1452.01
Screw	2	1.2/1.6/2.0/2.4	-	2-pole	-	KP01.1352.01
Screw	3	1.2/1.6/2.0/2.4	-	1-pole	-	KP01.1453.01
Screw	3	1.2/1.6/2.0/2.4	-	2-pole	-	KP01.1353.01

 $A \textit{vailability for all products can be searched real-time:} \\ \textit{http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER} \\$ 

Suffix "21" corresponds to the version with V-Lock mating cordset. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.

Type KP without cover: KP01.XXXX.XX90

Ground Terminal with solder pin: KP01.XXXX.X3XX

Packaging unit

50 Pcs

# **Mating Outlets/Connectors**

#### Category / Description



#### Appliance Outlet Overview complete

	4787
IEC Appliance Outlet F, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal	4788
IEC Appliance Outlet F or H, Screw-on Mounting, Front Side, Solder, PCB or Quick-connect Terminal	5091

Appliance Outlet further types to KP (FH)

### Connector Overview complete



IEC Connector C13, Rewireable, Straight	4782
IEC Connector C13, Rewireable, Straight	4022
IEC Connector C13, Rewireable, Angled	4785
IEC Connector C13, Rewireable, Angled	4300-06
IEC Connector C13, Rewireable, Angled	4012
Connector further types to KP (FH)	

### **Mating Outlets/Connectors shuttered**



Power Cord Overview complete

Overview Power Supply Cord with IEC Connector C13, V-Lock, straight VAC13KS

Power Cord further types to KP (FH)