




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **TPA (Terminal Position Assurance)**

Number of Positions: **5**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Hardware Accessory Function: **Position Assurance**

Features

Product Type Features

Connector Hardware Accessory Type	TPA (Terminal Position Assurance)
Hardware Accessory Function	Position Assurance

Configuration Features

Number of Positions	5
---------------------	---

Dimensions

Product Width	5.93 mm[.233 in]
Product Length	26.2 mm[1.03 in]
Product Height	4.35 mm[.171 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features



Packaging Method	Bag/Box
Packaging Quantity	10000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1969609-3
3P VAL-U-LOK TPA 26-22 AWG



TE Part # 1969609-1
1P VAL-U-LOK TPA 26-22 AWG



TE Part # 1-1969609-2
12P VAL-U-LOK TPA 26-22 AWG



TE Part # 1969609-8
8P VAL-U-LOK TPA 26-22 AWG





TE Part # 1-1969609-0
10P VAL-U-LOK TPA 26-22 AWG



TE Part # 1969608-5
5P VAL-U-LOK TPA 22-18 AWG




TE Part # 1-1969609-1
11P VAL-U-LOK TPA 26-22 AWG



TE Part # 1969609-2
2P VAL-U-LOK TPA 26-22 AWG



TE Part # 1969609-6
6P VAL-U-LOK TPA 26-22 AWG



TE Part # 1969609-4
4P VAL-U-LOK TPA 26-22 AWG




TE Part # 2432643-5
5P VAL-U-LOK TPA 26-22 AWG


Customers Also Bought



TE Part #1969609-8
8P VAL-U-LOK TPA 26-22 AWG



TE Part #1969597-6
6P RCPT VAL-U-LOK V2




TE Part #3-520132-2
ULTRAFAST 250 ASSY FLAG REC 16-14 TPBR




TE Part #316088-1
2.5 SIGNAL D/LOCK CAP HSG 4P



TE Part #4-928247-4
STD TIMER GEH 4P




TE Part #2238018-1
VAL-U-LOK PIN BR SN 22-26AWG



TE Part #1969597-2
2P RCPT VAL-U-LOK V2



TE Part #4-520447-2
ULTRA-FAST 250 ASY REC 12-10 AWG TPBR



TE Part #2296207-8
8P PM PLUG VAL-U-LOK PM GWT/V0

Documents



Product Drawings

5P VAL-U-LOK TPA 26-22 AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1969609-5_C1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1969609-5_C1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1969609-5_C1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773730-3 VAL-U-LOK Connectors with TPA Flyer

English

Product Specifications

Application Specification

English