

Features

- IC pin cutter. With small cutting edges, angled at 50°, suitable for cutting pins that are very close to each other.
- Steel thickness 2mm.
- For copper wire Ø 0.64 mm (22 awg).
- Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.
- Ergonomic anti-slip bicomponent handle for a safe, light and comfortable grip.
- Anti-reflection phosphating surface treatment.
- ESD-safe handles.
- Laser marking.
- Made in Italy.

RS PRO ESD IC pin cutter, angled at 50°. Micro head.

RS Stock No.: (0429712)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Made in Italy with high carbon steel and undergo a controlled atmosphere heat treatment.*
- *50° angled IC pin cutter with small cutting edges.*
- *The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.*
- *The tools are joined with grounded holes and surfaces, thereby allowing precise movements.*
- *The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours.*
- *ESD-safe version.*

General Specifications

Cutter Type	IC pin cutter with small cutting edges, angled at 50°. Micro head.
Material	High carbon steel
ESD Safe	YES. Standard IEC 61340-5-1

Mechanical Specifications

Cutting capacities	Ø 0.64mm (22 awg) copper wire
Cutting force	2 kg
Steel thickness	2 mm
Blade angle	50°
Overall Length	129 mm
Weight	50 g

