

SAFETY DATA SHEET
TOLUENE FREE ACRYLIC COATING AEROSOL

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name TOLUENE FREE ACRYLIC COATING AEROSOL
Product No. TFA-a, ETFA200H, ZE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Conformal coating for appliance protection
Uses advised against At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available

1.3. Details of the supplier of the safety data sheet

Supplier ELECTROLUBE. A division of HK
WENTWORTH LTD
ASHBY PARK, COALFIELD WAY,
ASHBY DE LA ZOUCH, LEICESTERSHIRE
LE65 1JR
UNITED KINGDOM
+44 (0)1530 419600
+44 (0)1530 416640
info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm GMT Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards	Flam. Aerosol 1 - H222
Human health	Acute Tox. 4 - H312; Acute Tox. 4 - H332; Skin Irrit. 2 - H315; Eye Irrit. 2 - H319
Environment	Not classified.

Classification (1999/45/EEC) Xn; R20/21. Xi; R36/38. F+; R12.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Physical and Chemical Hazards

Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

2.2. Label elements

Contains XYLENE

Label In Accordance With (EC) No. 1272/2008



Signal Word

Danger

TOLUENE FREE ACRYLIC COATING AEROSOL**Hazard Statements**

H222	Extremely flammable aerosol.
H312	Harmful in contact with skin.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.

Precautionary Statements

P210	Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P280	Wear protective gloves, eye and face protection.
P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P313	Get medical advice/attention.
P410+412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F.

Supplementary Precautionary Statements

P211	Do not spray on an open flame or other ignition source.
P251	Pressurized container: Do not pierce or burn, even after use.
P261	Avoid breathing vapour/spray.
P332+313	If skin irritation occurs: Get medical advice/attention.

2.3. Other hazards

Not Classified as PBT/vPvB by current EU criteria.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS**3.2. Mixtures**

XYLENE		30-60%
CAS-No.: 1330-20-7	EC No.: 215-535-7	
Classification (EC 1272/2008) Flam. Liq. 3 - H226 Acute Tox. 4 - H312 Acute Tox. 4 - H332 Skin Irrit. 2 - H315	Classification (67/548/EEC) R10 Xn;R20/21 Xi;R38	
BUTANONE		10-30%
CAS-No.: 78-93-3	EC No.: 201-159-0	Registration Number: 01-2119457290-43
Classification (EC 1272/2008) Flam. Liq. 2 - H225 EUH066 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R66 R67	
BUTANE		10-30%
CAS-No.: 106-97-8	EC No.: 203-448-7	
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12	

TOLUENE FREE ACRYLIC COATING AEROSOL

SOLVENT NAPHTHA (petroleum, light)		<0.5%
CAS-No.: 64742-95-6	EC No.: 265-199-0	
Classification (EC 1272/2008) Not classified.	Classification (67/548/EEC) Xn;R65. Xi;R37. N;R51/53. R10.	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

Ingestion

Rinse mouth thoroughly. Provide rest, warmth and fresh air.

Skin contact

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

4.3. Indication of any immediate medical attention and special treatment needed

Treat Symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

Unusual Fire & Explosion Hazards

Aerosol cans may explode in a fire. Risk of explosion if heated.

Specific hazards

Aerosol containers can explode when heated, due to excessive pressure build-up. Vapours may be ignited by a spark, a hot surface or an ember. Vapours are heavier than air and may travel along the floor and in the bottom of containers. Vapours may be ignited by a spark, a hot surface or an ember.

5.3. Advice for firefighters

Special Fire Fighting Procedures

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

TOLUENE FREE ACRYLIC COATING AEROSOL

6.2. Environmental precautions

Do not discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Absorb with inert, damp, non-combustible material, then flush area with water.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. For waste disposal, see section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
BUTANE	WEL	600 ppm	1450 mg/m ³	750 ppm	1810 mg/m ³	
BUTANONE	WEL	200 ppm	600 mg/m ³	300 ppm	899 mg/m ³	Sk
XYLENE	WEL	50 ppm	220 mg/m ³	100 ppm	441 mg/m ³	Sk

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

BUTANONE (CAS: 78-93-3)

DNEL

Industry	Dermal	Long Term	1161	mg/kg/day
Industry	Inhalation.	Long Term	600	mg/m ³
Consumer	Dermal	412	mg/kg/day	
Inhalation.	106	mg/m ³		
Oral	31	mg/kg/day		

PNEC

Freshwater	55.8	mg/l
Marinewater	55.8	mg/l
STP	709	mg/l
Sediment	284.7	mg/kg
Soil	22.5	mg/kg

8.2. Exposure controls

Protective equipment



Process conditions

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

Engineering measures

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

TOLUENE FREE ACRYLIC COATING AEROSOL

Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment. It is recommended to use respiratory equipment with combination filter, type A2/P2. EN14387

Hand protection

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Nitrile gloves are recommended. Gloves should conform to EN374

Eye protection

Wear approved, tight fitting safety glasses where splashing is probable.

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Aerosol.
Colour	Colourless.
Odour	Solvent.
Viscosity	60-80 cP @20°C (68 F)
Flash point (°C)	-4°C (24.8 F)

9.2. Other information

Volatile Organic Compound (VOC) 85%

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

No specific reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not available.

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.

10.5. Incompatible materials

Materials To Avoid

Strong acids. Strong alkalis. Strong oxidising substances.

10.6. Hazardous decomposition products

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Inhalation

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system.

TOLUENE FREE ACRYLIC COATING AEROSOL

Skin contact

Harmful in contact with skin. Prolonged or repeated exposure may cause severe irritation. Product has a defatting effect on skin.

Eye contact

Irritating to eyes.

Route of entry

Inhalation. Skin and/or eye contact.

Toxicological information on ingredients.

BUTANE (CAS: 106-97-8)

Acute toxicity:

Acute Toxicity (Inhalation LC50)

658 mg/l (vapours) Rat 4 hours

XYLENE (CAS: 1330-20-7)

Acute toxicity:

Acute Toxicity (Oral LD50)

3523 mg/kg Rat

Acute Toxicity (Dermal LD50)

12126 mg/kg Rabbit

Acute Toxicity (Inhalation LC50)

2700 mg/l (vapours) Rabbit 4 hours

Aspiration hazard:

Inhalation

Harmful by inhalation. Upper respiratory irritation. Central nervous system depression. Vapours may cause drowsiness and dizziness.

Ingestion

Swallowing concentrated chemical may cause severe internal injury. May cause nausea, headache, dizziness and intoxication. Diarrhoea.

Skin contact

Harmful in contact with skin. Irritating to skin.

Eye contact

May cause severe irritation to eyes.

Target Organs

Central nervous system Liver Kidneys

BUTANONE (CAS: 78-93-3)

Toxic Dose 1 - LD 50

>2193 mg/kg (oral rat)

Acute toxicity:

Acute Toxicity (Oral LD50)

> 2193 mg/kg Rat

Acute Toxicity (Dermal LD50)

> 5000 mg/kg Rabbit

Aspiration hazard:

Inhalation

Vapour may irritate respiratory system or lungs. Vapours may cause drowsiness and dizziness.

Ingestion

May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.

Skin contact

Irritating to skin. Repeated exposure may cause skin dryness or cracking.

Irritating to eyes.

TOLUENE FREE ACRYLIC COATING AEROSOL

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

No data on possible environmental effects have been found. Not regarded as dangerous for the environment.

12.1. Toxicity

12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

Not known.

SECTION 13: DISPOSAL CONSIDERATIONS

General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

13.1. Waste treatment methods

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

General

This product is packed in accordance with the Limited Quantity Provisions of CDGCPL2, ADR and IMDG. These provisions allow transport of aerosols of less than 1litre packed in cartons of less than 30kg gross to be exempt from control providing that they are labelled in accordance with the requirements of these regulations to show that they are being transported as Limited Quantities. Aerosols not so packed must show the following

14.1. UN number

UN No. (ADR/RID/ADN)	1950
UN No. (IMDG)	1950
UN No. (ICAO)	1950

14.2. UN proper shipping name

Proper Shipping Name	AEROSOLS
----------------------	----------

14.3. Transport hazard class(es)

ADR/RID/ADN Class	2.1
ADR/RID/ADN Class	Class 2: Gases
ADR Label No.	2.1
IMDG Class	2.1
ICAO Class/Division	2.1
Transport Labels	

TOLUENE FREE ACRYLIC COATING AEROSOL

**14.4. Packing group**

Not applicable.

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

14.6. Special precautions for user

EMS F-D, S-U

Tunnel Restriction Code (D)

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**Statutory Instruments**

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716). Control of Substances Hazardous to Health.

Guidance Notes

Workplace Exposure Limits EH40.

EU Legislation

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

Issued By	Helen O'Reilly
Revision Date	APRIL 2013
Revision	3
SDS No.	12823

TOLUENE FREE ACRYLIC COATING AEROSOL**Risk Phrases In Full**

R12	Extremely flammable.
R10	Flammable.
R20/21	Harmful by inhalation and in contact with skin.
R65	Harmful: may cause lung damage if swallowed.
R11	Highly flammable
R36/38	Irritating to eyes and skin.
R36	Irritating to eyes.
R37	Irritating to respiratory system.
R38	Irritating to skin.
R66	Repeated exposure may cause skin dryness or cracking.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.

Hazard Statements In Full

EUH066	Repeated exposure may cause skin dryness or cracking.
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H312	Harmful in contact with skin.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H336	May cause drowsiness or dizziness.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.