

**Jelt**

PRODUCT DATA SHEET

ULTRA NET ALIMENTAIRE

DEGREASING CLEANING AGENT FOR CONTACT WITH FOODSTUFFS

1. MAIN CHARACTERISTICS

Versatile cleaning agent, ready for use, for all surfaces.

- Has a strong degreasing power.
- Fully water-soluble.
- Eliminates animal, vegetable and mineral grease
- Erases traces of ink, dye and stubborn emulsions.
- Cleans without tarnishing and scratching surfaces.
- Usable as a detergent before using the BACTOCLEAN disinfectant Ref.: 748075
- It is used on all types of surfaces.

2. SCOPE OF APPLICATION

- Agro-food industries
- Communities
- Kitchens
- Food shops
- Printing shops
- Bars, restaurants
- Refrigerated trailers

3. DIRECTIONS FOR USE

- Spray ULTRA NET ALIMENTAIRE directly on the surfaces to be cleaned.
- Rub if necessary with a wipe.
- Rinse with fresh water.
- Wipe with a clean cloth.

4. PHYSICOCHEMICAL CHARACTERISTICS

- Appearance: Clear liquid
- Colour: Colourless
- Density of the PA (20°C): 1.015 g/cm³ +/-0.015
- Odour: Neutral
- pH: 10.5 +/- 0.5
- Contains among other ingredients (EC Regulation No. 648/2004): Isopropyl alcohol

5. PRECAUTION OF USE - LABELLING

Product for professional use. Refer to the safety data sheet.

6. PACKAGING AND STORAGE

750ml spray (12 / crate). Reference 747750.

Keep it away from light, heat and cold.

Storage temperature: 0°C to 45°C

Safety data sheets are available on the Internet: <http://www.jelt.fr>

FAITES ÉQUIPE AVEC LA PERFORMANCE

This product information was created on 27/07/2016 and cancels all previous information. The information supplied is based on our knowledge and experience to date. Please be aware of the potential risks to users that may occur when the product is used for purposes other than for which it was designed. In no way does this exempt the user from knowing and applying all regulations related to their activity. The product's user is solely responsible for taking the necessary precautions for the product.

ITW Spraytec - 5 bis rue Retrou - 92600 ASNIERES SUR SEINE - Tel. 01.40.80.32.32 Fax 01.40.80.32.40