

RF-17S1N8AWV00 - Device connector front mounting



1613740

<https://www.phoenixcontact.com/gb/products/1613740>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, straight, Screw locking mechanism, M23, number of positions: 17, contact connection type: Socket, Axial O-ring, shielded: yes, number of positions: 17, connection method: Crimp connection, series: RF

Commercial data

Item number	1613740
Packing unit	20 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Sales key	ABRAGL
Product key	ABRAGL
GTIN	4046356443913
Weight per piece (including packing)	41.995 g
Weight per piece (excluding packing)	38.238 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Order information:

Order crimp contacts Ø 1 mm separately

Mounting

Mounting type

Front mounting/square flange 4x Ø 3,2 mm

Assembly note

4x Ø 3,2 mm

Product properties

Product type

Circular connectors (device side)

Series

RF

Application

Signal

Number of positions

17

Connection profile

17

Shielded

yes

Coding

N

Thread type

M23

Material specifications

Seal material

FPM

Housing material

High-grade steel 1.4305

Electrical properties

Contact

Contact diameter

1 mm

Max. current

8 A

Nominal voltage U_N

48 V AC 74 V DC

Overvoltage category

III

Degree of pollution

3

Rated surge voltage

1.5 kV

Connection data

Conductor connection

Connection method

Crimp connection

Contact connection type

Socket

Connector

Type

straight

Direction of rotation

Standard

Environmental and real-life conditions

Ambient conditions

RF-17S1N8AWV00 - Device connector front mounting




1613740

<https://www.phoenixcontact.com/gb/products/1613740>

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m


Drawings

Dimensional drawing



Installation dimensions

Dimensional drawing



Dimensional drawing

RF-17S1N8AWV00 - Device connector front mounting




1613740

<https://www.phoenixcontact.com/gb/products/1613740>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1613740>

	cUL Recognized Approval ID: E153698-20090723			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	1 A	26	-

	UL Recognized Approval ID: E153698-20090723			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	1 A	26	-

RF-17S1N8AWV00 - Device connector front mounting



1613740

<https://www.phoenixcontact.com/gb/products/1613740>

Classifications

ECLASS

ECLASS-13.0	27440109
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1613740

<https://www.phoenixcontact.com/gb/products/1613740>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk