




Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**  
Contact Mating Area Plating Material: **Gold Flash**  
Wire Size: **.2 – .6 mm²**  
Connector System: **Wire-to-Wire**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Contact Features

Contact Mating Area Plating Material	Gold Flash
Contact Type	Socket
Mating Pin Diameter	1 mm[.039 in]
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material Thickness	.762 µm[30 µin]
Wire Contact Termination Area Plating Thickness	.76 µm[30 µin]
Wire Contact Termination Area Plating Material	Tin-Lead
Contact Orientation	Right Angle
Contact Underplating Material	Nickel
Contact Size	20

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

--	--



Wire Size	.2 – .6 mm²
-----------	-------------

Accepts Wire Insulation Diameter Range	1.57 mm[.062 in]
--	------------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Bag
------------------	-----

Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Not Yet Reviewed
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 91544-1  
CCII TYPE XI PIN SKT 24-20 ASSY




TE Part # 91544-3  
CCII TYPE XI PIN SKT 24-20 HEAD

Customers Also Bought



TE Part #2141467-2  
2POS,NANOMQS,SOCK HSG,ASSY, SEALED,CODB



TE Part #807551-000  
202D221-4/42-0



TE Part #3-647106-5  
05P MTA-100 HDR ASSY,SM,SN



TE Part #1-1393030-0  
SSR SRS,PANEL MNT, 50A,240V AC - DC I/P



TE Part #3-641208-7  
07P MTA156 HDR ASSY FL ST LF



TE Part #1-225550-8  
TNC PLUG



TE Part #837567-000  
101A011-25/86-0

Documents

Product Drawings  
CONTACT ASSY.-SOC.(L.P.)

English

Datasheets & Catalog Pages  
Products for Aerospace and Defense

English

Product Specifications  
Application Specification

English

Type XI Contact

English