

## Features

- Euro Plug Top
- DOE Level VI Efficiency
- 1 x USB A Socket
- Compact Design
- 5 Watts

## RS PRO AC/DC Adapters

RS Stock No.: 0360639



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

# AC/DC Adapters

## Product Description

This compact 5vdc 1amp Euro Plug Top power supply is suitable for charging USB products with a maximum load of 1amp via an Integral USB A Socket

- Euro Plug Top
- Integral USB A Socket

## General Specifications

Type	Switched Mode Power Supply
Input Plug Type	EU Plug Top
Output Connector	USB A Socket
Input Connector	EU Plug
Cable Length	N/A
Cable Type	N/A
Power Indicator	No
Over Current Protection	Yes
Short Current Protection	Yes
Over Current Protection	Yes
MTBF	50000 hours at maximum load
Medical Approval	No

### Electrical Specifications

#### Input Specifications

Rated Input Voltage	100 to 240V ac
Full Input Voltage Range	90 – 264V ac
Rated Frequency	50/60Hz
Full Frequency Range	47/63Hz
Efficiency	74%
Input Current (RMS Max.)	0.3A
Inrush Current	40A Max
Leakage Current (max.)	0.25mA / 240V ac
Input Protection	Thermal fuse in Primary; Current Limit, Short Circuit

#### Output Specifications

Output Voltage	5V dc	
Maximum No load Voltage	5V dc	
Output Maximum Current	1amp	
Output Minimum Current	0A	
Output Regulation	+/-5%	
Rated Power	5W	
Start Up Delay	20ms	
Start Up Rise Time	20ms	
Hold Up Time	20ms	
Number of Outputs	1	
Efficiency	74%	
Efficiency Level	VI	
Output Voltage Precision	5%	
Ripple & Noise	200mV	
Turn On Delay	4 Seconds Max.	
Insulation Class	II	
Switching Frequency	70KHz	
Isolation Resistance	100MΩ @500V dc	
Voltage Isolation	Input-Output	3000V ac
	Input-Ground	
	Output-Ground	

### Mechanical Specifications

Dimension	
Length	41mm
Width	33mm
Depth	21mm
Weight	40g

# AC/DC Adapters

## Operation Environment Specifications

Operating Humidity	20% to 85% RH non-condensing
Cooling	Natural convection
Operating Temperature Range	0 to 40°C
Storage Temperature Range	-20 to 80°C
Altitude During Operation	3000m
Vibration Resistance	To IEC-68-2-6

## Approvals

Compliance/Certifications	<u>CE</u>
Declarations	MFR Declaration of Conformity
Medical Approval	NO

