

## Magnetic label - PMM (EX25)R YE - 1014308

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Magnetic label, Roll, yellow, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Magnetic adhesion, Lettering field: 15000 x 25 mm

### Why buy this product

- Magnetic labels, unprinted
- The magnetic labels supplied in rolls represent an individual and flexible marking solution, e.g., for warehouse marking.
- High adhesive strength
- The flexible magnetic tape will also adhere to round objects with a radius from 12 mm
- Magnetic tape coated with polyester foil

### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 786126
Weight per Piece (excluding packing)	756.1 g
Custom tariff number	39207380
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	15000 mm
Width (a)	25 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 55 °C
---------------------------------	------------------

#### General

Color	yellow
Material	Magnetic tape
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1
Number of individual labels per row	1

# Magnetic label - PMM (EX25)R YE - 1014308

## Technical data

### General

Marking mounting type	Magnetic adhesion
-----------------------	-------------------

## Classifications

### eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27371301
eCl@ss 5.1	27371301
eCl@ss 6.0	27371301
eCl@ss 7.0	27371301
eCl@ss 8.0	27141137

### ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777

### UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107

## Accessories

### Accessories

#### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black