

**BOSCH**

Invented for life

Power tools for trade &amp; industry

# Product data sheet



Cordless Drill/Drivers

## GSR 18 V-EC FC2

Bosch FlexiClick 5-in-1 System: Masters any challenge

### The most important data

Battery voltage	18 V
Max. screw diameter	10 mm
Torque, max. (hard/soft)	50 / 31 Nm

**Part number:** 0 601 9E1 102**from GBP 119,00\***[> More product information](#)*\* Recommended retail price excluding VAT*

### Technical data

Torque, max. (hard/soft)	50 / 31 Nm
No-load speed (1st gear / 2nd gear)	0 – 500 / 0 – 1.700 rpm
Max. impact rate	4.800 bpm
Chuck capacity, min./max.	1,5 / 13 mm
Battery voltage	18 V
Battery capacity	4,0 Ah
Weight incl. battery	1,7 kg
Torque settings	18+1
Length	147,0 mm
Cell type	Lithium-ion
Bit holder	1/4" internal hexagon
<b>Drilling diameter</b>	
Max. drilling diameter in wood	38 mm
Max. drilling diameter in steel	13 mm
<b>Screw diameter</b>	
Max. screw diameter	10 mm

### Noise/vibration information

<b>Screwdriving</b>	
Vibration emission value ah	2.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>
<b>Drilling in metal</b>	
Vibration emission value ah	2.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

**BOSCH**

Invented for life

**Power tools for trade & industry****Advantages:**

- Full flexibility – With its bit holder, drill chuck adapter, angle adapter, off-set angle adapter and rotary hammer adapter, the Bosch FlexiClick system provides the optimum solution in every work situation
- Easy to operate – The Bosch FlexiClick adapters can be locked in 16 different positions (360°) without having to remove them from the cordless screwdriver
- Versatile – The unique rotary hammer adapter turns the drill/driver into a fully fledged rotary hammer
- Integrated lockable bit holder accepts all common standard bits
- Compact design – Short construction (147 mm) and low weight (1.7 kg, GSR 18 V-FC2) enable precise use
- High efficiency – up to 826 screws (6 x 60 mm in softwood) with only one battery charge (18 V – 4.0 Ah)



dynamicseries

**Prices / Scope of delivery**

Part number	0 601 9E1 170	0 601 9E1 171	0 601 9E1 102
1/2 L-BOXX inlay for attachments 2 608 438 129	✓	✓	✓
1/2 L-BOXX inlay for tool 2 608 438 093	✓	✓	✓
2 x 4.0 Ah Li-Ion batteries 1 600 Z00 038	✓	✓	-
AL 1860 CV quick charger 2 607 225 324	✓	✓	-
Battery and charger not included	-	-	✓
GEA FC2 off-set angle adapter 1 600 A00 1SJ	✓	-	-
GFA FC2 drill chuck adapter 13 mm 1 600 A00 1SL	✓	✓	✓
GHA FC2 rotary hammer adapter 1 600 A00 3NF	✓	-	-
GWA FC2 angle adapter 1 600 A00 1SK	✓	-	-
L-BOXX 136 1 600 A00 1RR	✓	✓	✓
<b>Price</b> (Recommended retail price excluding VAT)	<b>GBP 459,00</b>	<b>GBP 309,00</b>	<b>GBP 119,00</b>