


ABT-607 Pneumatic Crimper

The ABT-607 is a pneumatic powered and controlled machine. It is designed for customers with moderate volume. This machine is designed to semi-automatically crimp stamped and formed contacts onto pre-stripped stranded or single conductor electrical wire. This machine will accommodate size 34 thru 12 AWG wire and is actuated by the use of a footpedal.

Machine Crimp: 800 per hour

Power Requirements: Pneumatic = 100 psi, 2 cu. ft. per min.

ABT-607



Products: D*A, MDSM, 75 OHM Crimp Coax

ABT-620 Semi-Automatic Crimper/Stripper

The ABT-620 Universal Cannon Crimper/Stripper is a pneumatic powered, microprocessor controlled machine. It is designed to semi-automatically strip insulation from stranded or single conductor electrical wire and attach a stamped and formed contact by crimping. The machine will accommodate 34 thru 12 AWG wire. Primary application of the machine is the termination of jacketed cable where the individual leads cannot be stripped on fully automated equipment. The ABT-620 UCCS operates automatically upon insertion of a wire or it can be switched over to foot pedal operation as desired.

Machine Strip/Crimp Rate: 1200+ per hour

Power Requirement: Electrical = 115 VAC, 60 Hz, 20 A
Pneumatic = 80 psi, 2 cu. ft. per min.

ABT-620 UCCS



Products: D*A, MDSM,

Insertion/Extraction Tools

D*A
CIET-D*A-20-24
980-0008-135
(20 - 24 AWG)

CIET-D*A-24-26
980-0008-136
(24 - 26 AWG)

ZD-HD
CIET-22DF
980-0004-804

Hand - Crimp Tool

D*A Contacts
CCT-D*A-1 995-2000-000

ZD HD (size 22 contacts)
CCT-22D 995-2000-022

