

## Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 13.02.2019

Version number 11

Revision: 13.02.2019

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** UHU stic 21g (12) GB/E/P/I
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**  
No further relevant information available.
- **Application of the substance / the mixture** Adhesives
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
UHU GmbH & Co.KG  
Herrmannstraße 7  
D-77815 Bühl (Baden)  
Tel.: 0049-(0)7223-284-0  
email: sds@uhu.boltongroup.com
- Fax: 0049-(0)7223-284-245
- **Further information obtainable from:** UHU QESH
- **1.4 Emergency telephone number:**  
Tel.: + 49 (0) 30/19240 (Notruf)  
Tel.: + 49 (0) 72 23/28 40

### SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**  
The product is not classified, according to the CLP regulation.

---

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008** Void
- **Hazard pictograms** Void
- **Signal word** Void
- **Hazard statements** Void
- **Precautionary statements**  
P210 Keep away from open flames. - No smoking.  
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P501 Dispose of contents/container in accordance with local/regional/national/international regulations.
- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**
- **Description:**  
Mixture of substances listed below with nonhazardous additions.  
Adhesive

(Contd. on page 2)

## Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 13.02.2019

Version number 11

Revision: 13.02.2019

**Trade name: UHU stic 21g (12) GB/E/P/I**

(Contd. of page 1)

- **Dangerous components:** Void
- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

### SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** No special measures required.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:**  
Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed**  
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

### SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture**  
No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

### SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** No special measures required.
- **6.3 Methods and material for containment and cleaning up:**  
Send for recovery or disposal in suitable receptacles.  
Dispose contaminated material as waste according to item 13.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** No special measures required.
- **Information about fire - and explosion protection:** Keep ignition sources away - Do not smoke.

(Contd. on page 3)

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.02.2019

Version number 11

Revision: 13.02.2019

**Trade name: UHU stic 21g (12) GB/E/P/I**

(Contd. of page 2)

- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Storage class:** 13
- **7.3 Specific end use(s)** No further relevant information available.

### SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**

- **Ingredients with limit values that require monitoring at the workplace:**

**57-10-3 Palmitic acid**

MAK (Germany) | vgl.Abschn.IIb und Xc

**544-63-8 Myristic acid**

MAK (Germany) | vgl.Abschn.IIb und Xc

- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
The usual precautionary measures are to be adhered to when handling chemicals.
- **Respiratory protection:** Not required.
- **Protection of hands:**  
Not required.  
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**  
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**  
The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Not required.

EU-EN

(Contd. on page 4)

## Safety data sheet

### according to 1907/2006/EC, Article 31

Printing date 13.02.2019

Version number 11

Revision: 13.02.2019

**Trade name: UHU stic 21g (12) GB/E/P/I**

(Contd. of page 3)

**SECTION 9: Physical and chemical properties**
**· 9.1 Information on basic physical and chemical properties**
**· General Information**
**· Appearance:**

Form:	Solid
Colour:	Whitish
· Odour:	Characteristic
· Odour threshold:	Not determined.

· pH-value at 20 °C:	10.5
----------------------	------

**· Change in condition**

Melting point/freezing point:	64-65 °C
Initial boiling point and boiling range:	100 °C

· Flash point:	Not applicable.
----------------	-----------------

· Flammability (solid, gas):	Not determined.
------------------------------	-----------------

· Ignition temperature:	395 °C
-------------------------	--------

· Decomposition temperature:	Not determined.
------------------------------	-----------------

· Auto-ignition temperature:	Product is not selfigniting.
------------------------------	------------------------------

· Explosive properties:	Product does not present an explosion hazard.
-------------------------	---

**· Explosion limits:**

Lower:	0.0 Vol %
Upper:	0.0 Vol %

· Vapour pressure at 20 °C:	23 hPa
-----------------------------	--------

· Density at 20 °C:	1.08-1.1 g/cm <sup>3</sup>
---------------------	----------------------------

· Relative density	Not determined.
--------------------	-----------------

· Vapour density	Not applicable.
------------------	-----------------

· Evaporation rate	Not applicable.
--------------------	-----------------

**· Solubility in / Miscibility with water:**

Not miscible or difficult to mix.

· Partition coefficient: n-octanol/water:	Not determined.
---	-----------------

**· Viscosity:**

Dynamic:	Not applicable.
Kinematic:	Not applicable.

**· Solvent content:**

Water:	70.2 %
VOC (EC)	0.00 %

Solids content:	100.0 %
-----------------	---------

(Contd. on page 5)

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.02.2019

Version number 11

Revision: 13.02.2019

**Trade name: UHU stic 21g (12) GB/E/P/I**

(Contd. of page 4)

· **9.2 Other information**

All relevant physical data were determined for the mixture. All non determined data are not measurably or not relevant for the characterization of the mixture.

### SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

### SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Acute effects (acute toxicity, irritation and corrosivity)** Not applicable.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

### SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**  
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water  
Do not allow product to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 13.02.2019

Version number 11

Revision: 13.02.2019

**Trade name: UHU stic 21g (12) GB/E/P/I**

(Contd. of page 5)

- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

**SECTION 13: Disposal considerations**

- **13.1 Waste treatment methods**
- **Recommendation**  
Smaller quantities can be disposed of with household waste.  
Disposal must be made according to official regulations.

· **European waste catalogue**

08 04 10	waste adhesives and sealants other than those mentioned in 08 04 09
----------	---

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

**SECTION 14: Transport information**

· <b>14.1 UN-Number</b>	Void
· <b>ADR, IMDG, IATA</b>	-
· <b>ADN</b>	Void
· <b>14.2 UN proper shipping name</b>	Void
· <b>ADR, ADN, IMDG, IATA</b>	Void
· <b>14.3 Transport hazard class(es)</b>	
· <b>ADR, ADN, IMDG, IATA</b>	
· <b>Class</b>	Void
· <b>14.4 Packing group</b>	Void
· <b>ADR, IMDG, IATA</b>	Void
· <b>14.5 Environmental hazards:</b>	
· <b>Marine pollutant:</b>	No
· <b>14.6 Special precautions for user</b>	Not applicable.
· <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	Not dangerous according to the above specifications.
· <b>UN "Model Regulation":</b>	Void

EU-EN

(Contd. on page 7)

## Safety data sheet

### according to 1907/2006/EC, Article 31

Printing date 13.02.2019

Version number 11

Revision: 13.02.2019

**Trade name: UHU stic 21g (12) GB/E/P/I**

(Contd. of page 6)

#### SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

#### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** UHU QESH
- **Contact:** Dr. C. Hanf
- **Abbreviations and acronyms:**
  - ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
  - IMDG: International Maritime Code for Dangerous Goods
  - IATA: International Air Transport Association
  - GHS: Globally Harmonised System of Classification and Labelling of Chemicals
  - EINECS: European Inventory of Existing Commercial Chemical Substances
  - ELINCS: European List of Notified Chemical Substances
  - CAS: Chemical Abstracts Service (division of the American Chemical Society)
  - VOC: Volatile Organic Compounds (USA, EU)
  - PBT: Persistent, Bioaccumulative and Toxic
  - vPvB: very Persistent and very Bioaccumulative
- **\* Data compared to the previous version altered.**