

213.1630

PLUG
16A 2P+E 4h 100-130V 50Hz 60Hz
Screw terminals



* Product image may be indicative



EN IEC 60309-1 (2022)
 EN IEC 60309-2 (2022)

Low voltage direct. 2014/35/EU

■ GENERAL CHARACTERISTICS

Commercial Series	OPTIMA Series
Synthetical description	PLUG

Description

The plug from the OPTIMA Series is designed for a rated voltage of 100-130V and a current of 16A. Featuring 2P+E poles and a 4h hour position, it operates efficiently at both 50Hz and 60Hz frequencies. With a protection degree of IP44/IP54, it offers reliable performance in various environments. The plug is equipped with screw terminals and is compatible with straight type outlets. A version with a transparent handle is also available by appending ".TR" to the catalogue number. This plug is engineered to meet the demands of professional applications, ensuring dependable connectivity and durability.

Mounting version	PORTABLE
------------------	----------

■ TECHNICAL CHARACTERISTICS

Rated current	16A
Poles	2P+E
Hour position	4h
Rated voltage	100-130V
Working frequency	50Hz
	60Hz
Terminals	Screw terminals

■ PHYSICAL CHARACTERISTICS

Mounting version	PORTABLE
Colour	YELLOW
Material	THERMOPLASTIC
Protection degree	Splash proof
Protection degree IP	IP44/IP54
Protection degree IK	IK08
Types of available outlets	STRAIGHT
Contact material	CuZn (brass)
Surface treatment contacts	Nickel-plated
Cable entry	CABLE GLAND

■ DOWNLOAD

Technical drawing [PDF]
 Technical drawing [STP]
 Technical drawing [DWG]

■ OPTIONS & VARIOUS NOTES

Catalogue notes	Version also available with transparent handle; just add ".TR" at the end of the catalogue number.
-----------------	--