


Features

- Thermoresistances
- Max. operating temperature 400°C
- ¼" x 19" connector
- Protection tube Nickel Coated Brass
- Sensor type DIN/EN60751
- Cable type Fiber glass+Fiber glass+Braided
- Immersion Length 50mm
- Cable Length 1meter

RS PRO Standard Bayonet Type PT-1000 Thermoresistances With ¼" x 19" Connector

RS Stock No: 0350407



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Standard Bayonet Type PT1000 Thermoresistances Temperature Sensor

Diameter(M): 6mm

Immersion Length(L): 50mm

Cable Length(K): 1m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications

General Specifications

Max. Operating Temperature	-50 °C / +400 °C
Standard cable types	Fiber glass + fiber glass + braided wire
Sensor type	DIN/EN60751 Class "B" 1xPT-1000
Protection tube material	Nickel coated brass
Connector	Standard 1/4 x 19"

Mechanical Specifications

Diameter (M)	6mm
Immersion Length (L)	50mm
Cable Length (K)	1m

Electrical Connection

