

Article No. : 1FL2105-2AF01-1HB0



Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Basic motor data	
Motor type	Permanent-magnet synchronous motor
Motor type	Low Inertia
Static torque	5.00 Nm
Static current	4.65 A
Maximum torque	15.90 Nm
Maximum current	18.0 A
Maximum speed	6,000 rpm
Rotor moment of inertia	1.7100 kgcm ²
Weight	5.5 kg

Rated data	
SINAMICS S200, 3 AC 380 ... 480 V	
Rated speed	3,000 rpm
Rated torque	4.60 Nm
Rated current	4.3 A
Rated power	1.45 kW

Encoder system	
Encoder system	Absolute encoder singleturn 17 bit

Motor connection	
Connection type	Metal angular connector

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	52
Flange size (AB)	105 mm
Centering ring (N)	95 mm
Hole circle (M)	115 mm
Screw-on hole (S)	9.0 mm
Overall length (LB)	168.9 mm
Diameter of shaft (D)	19 mm
Length of shaft (E)	45 mm
Length of flange diagonal (P)	135 mm
Shaft end	Shaft with parallel key (half-key balancing)
Color of the housing	Anthracite RAL 7016

