




Connectors > Connector Accessories > Light Pipes



Form Factor: **SFP**

Number of Lightpipes: **4**

Lightpipe Product Type: **Lightpipe Kit**

Lightpipe Configuration: **Dual Square**

Features

Product Type Features

Form Factor	SFP
Lightpipe Product Type	Lightpipe Kit

Configuration Features

Number of Lightpipes	4
Lightpipe Configuration	Dual Square

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Packaging Features

Packaging Method	Tray
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2025 (250)

Candidate List Declared Against: JUNE 2025 (250)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1761394-1
DUST COVER, SFP, GANGED & STACKED

Customers Also Bought




TE Part #MS560702BA03-50
MS5607-02BA SS CAP ALTIMETER T&R





TE Part #280370-2
2P AMPMODU II SHRD HDR, ST, 0.38 AU



TE Part #749070-9
100 50SR VERT RCPT ASSY



TE Part #826648-8
08P AMPMODU II PIN HDR.



Documents

Product Drawings

SFP 1X2 LIGHT PIPE ASSY

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1761011-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1761011-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1761011-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English