




---

 PRODUCT-DETAILS

# BZH1000A-T-1P-M12-TK

## BZH1000A-T-1P-M12-TK Switch disconnecter




---

**General Information**

Extended Product Type	BZH1000A-T-1P-M12-TK
Product ID	1SEP622022R0001
EAN	3800161652745
Catalog Description	BZH1000A-T-1P-M12-TK Switch disconnecter
Long Description	<p>Cu+ switch disconnectors are specially engineered to perform in surroundings with high ambient temperatures and are available as 1P and 3P variants.</p> <p>All Cu+ switch disconnectors have been tested and approved for performance exceeding the requirements of IEC60947-1 and IEC60947-3. Enabling use in ambient temperatures up to 55°C (131°F) without requiring derating, the switches can be applied with 100% of the rated current Ie.</p> <p>Cu+ switch disconnectors are available for 1000A – 2000A and are factory equipped with optimized fuse knives.</p> <p>InLine II Cu+ replaces the old range of SLBM and BSL switches 1:1.</p>

---

**ABB EcoSolutions**

ABB Site Meeting Group Waste To Landfill Target	No non-hazardous waste is sent to a landfill UL 2799 Zero Waste To Landfill Validation available
End Of Life Disassembling	9AKK108470A6421

## Instructions

**Material Compliance**

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

**Popular Downloads**

Data Sheet, Technical Information	1SEC312023D0201
Instructions and Manuals	9AKK107680A5077
Mechanical Drawings	9AKK107680A8038 9AKK107991A5716 9AKK107991A5717
Electrical Drawings	9AKK108466A4607 9AKK108466A4606

**Environmental**

Degree of Protection	Front IP30
----------------------	------------

**Ordering**

Minimum Order Quantity	1 piece
Customs Tariff Number	85389099
Country or Territory of Origin	Bulgaria

**Dimensions**

Product Frame Size	High
Product Net Width	99 mm
Product Net Height	775 mm
Product Net Depth / Length	207 mm
Product Net Weight	14.8 kg

**Container Information**

Package Level 1 Units	box 1 piece
Package Level 1 Width	99 mm
Package Level 1 Depth / Length	207 mm
Package Level 1 Height	775 mm
Package Level 1 Gross Weight	15.5 kg
Package Level 1 EAN	3800161652745

## Technical

Degree of Protection	Front IP30
Device Type Manager (DTM)	Switch disconnecter
Distance Between Phases	185 mm
Electronic Fuse Monitoring	No
Fuse Size	Solid link
Fuse System	DIN
Handle Type	1P
Number of Poles	3P
Power Loss	at Rated Load 253.3 W
Rated Current ( $I_n$ )	Main Circuit 1000 A
Rated Impulse Withstand Voltage ( $U_{imp}$ )	Main Circuit 8 kV
Rated Insulation Voltage ( $U_i$ )	1000 V
Rated Operational Current AC-20B	(690 V) 1000 A (500 V) 1000 A
Rated Operational Current AC-21B ( $I_e$ )	(690 V) 1000 A (500 V) 1000 A
Rated Operational Current AC-22B ( $I_e$ )	(500 V) 1000 A
Rated Operational Voltage	500 V AC
Rated Short-Circuit Making Capacity ( $I_{cm}$ )	15 kiloampere rms
Rated Short-time Withstand Current Low Voltage ( $I_{cw}$ )	(730 V AC) 15 kiloampere rms for 1 s 15 kiloampere rms
Standards	IEC60947-3
Terminal Type	Bolt
Tightening Torque	35 N·m

## Technical UL/CSA

Tightening Torque	35 N·m
-------------------	--------

## Certificates and Declarations

Declaration of Conformity - CE	1SEP500046P0001
--------------------------------	-----------------

## External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC001040 - Fuse switch disconnecter
ETIM 10	EC000216 - Switch disconnecter (AC)
eClass	V11.1 : 27371401
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

---

## Categories

---

Low Voltage Products and Systems → Fusegear → Fuse Switch Disconnectors → Inline II

