



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	Documentation CD User manual Warranty card
--------------------	--

### Physical

Colour	Black
Depth	59.4 cm
Height	43.2 cm
Net weight	40.6 kg
Width	8.5 cm

### Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 % non-condensing
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m

### Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Battery voltage	96 V
Battery type	Lead-acid battery
Number of battery replacement quantity	2

## Packing Units

Package 1 Weight	44.5 kg
Package 1 Height	23.9 cm
Package 1 width	59.9 cm
Package 1 Length	83.1 cm
Number of Units in Package 3	6

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------