




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 3 – 6 mm²

Stud Size: #8

Stud Diameter: 4.3 mm [.169 in]

Features

Product Type Features

Shape Description	RING-008
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	1 g[.03527 oz]
Insulation Sleeve Color	Yellow

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	3 – 6 mm ²
-----------	-----------------------



Stud Diameter	4.3 mm[.169 in]
Tongue Thickness	.99 mm[.039 in]
Product Length	38 mm[1.496 in]
Barrel Inside Diameter	6.5 mm[.256 in]

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	500
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # EG8162-000
[HL1920E-230V-EURO](#)


Customers Also Bought



TE Part #AS608-35SA
[PLUG BOOT TERMIN'N TYPE 6](#)



TE Part #1-6609032-5
[10VR6=F7359 S0](#)



TE Part #697233-000
[B-106-1503](#)



TE Part #AS012-35PN
[RECEPT.2 HOLE MNT.TYPE 0](#)



TE Part #5-1879208-0
[CPF 0402 1K1 0.1% 25PPM 1K RL](#)



TE Part #AS614-35SA
[PLUG.BOOT TERMIN.N TYPE 6](#)




TE Part #AS610-03SN
[PLUG BOOT TERMINN TYPE 6](#)



TE Part #AS110-03PN
[RECEPT.IN-LINE. MNT.TYPE 1](#)



TE Part #154719-4
[PL 250 REC HSG 1P NYLON YELLOW](#)



TE Part #857409-000
[B-106-1992](#)

Documents

Product Drawings

[B-106-1403](#)

English

CAD Files

[3D PDF](#)



3D

Customer View Model

[ENG_CVM_CVM_164581-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_164581-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_164581-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654025_Sec8_B-106](#)

English

Product Specifications

[Installation Procedure for Duraseal Splices and Terminals](#)

English