

Fan LXT®

DCF201

18V • ø 250 mm • 17 m³/min

Efficient fan with two air flow settings and a timer

An efficient cordless table top fan with two air flow settings and a timer function. Brings added comfort in hot weather and speeds up drying of paint or filler. Includes a mains adapter.



Technical specifications

Max. Air Velocity	2,32 m/s
Nominal Battery Voltage	14,4 / 18 V
Sound Power Level (L _{WA})	67,3 dB(A)
Product Dimensions (L x W x H):	263 x 330 x 523 mm
Tool weight with battery	2,5 - 2,9 kg
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Voltage LXT	✓
Continuous Use 14.4V / 3.0 Ah Battery	180 / 90 min
Continuous Use 18V / 3.0 Ah Battery	200 / 100 min
Continuous Use 18V / 5.0 Ah Battery	380 / 190 min
Continuous Use 18V / 6.0 Ah Battery	460 / 230 min
Product net weight	2,1 kg
Diameter (D)	250 mm
Angle range vertical	45 °

User benefits

- Automatic timer switch-off after 1, 2 or 4 hours
- Battery protection system automatically shuts off power when the battery level is low
- 3-stage automatic timer with 1, 2, and 4 hour power-off selection
- Powered by Makita LXT® Li-ion battery or AC adapter

Link to product - www.makitauk.com



Related products

■ Other

Parts drawing