



Gas Control Equipment



## PREMIUM CYLINDER REGULATOR SERIES

# GCE ProControl®

*"We challenged our skilled engineers to develop an improved version of our top-seller Dincontrol® which has been presented in the market for over 18 years and has become a leader among the premium cylinder regulators in terms of **Accuracy, Safety, and Reliability**. We made a few modifications to maintain the focus on these three main features. From customer feedback, we have seen the most vulnerable part of the regulator has been the gauges. We are now adding **Durability** to the features of GCE ProControl® by **protecting the gauges** to minimise the risk of breakdown and user productivity interruption. The investment in gauge protection is paid back in a very short time."*

GCE Team

### HIGHLY DURABLE REGULATOR

Mechanical damages are the most frequent and most costly reason for regulator failure. It happens usually during transport of the installed oxy-fuel sets, during cylinder exchange or when transporting heavy parts and constructions on the cranes in the welding areas. The improved, robust gauge protection minimizes production breaks, service, and replacement cost and saves the gas leaking through broken gauges.

### HIGH OPERATION SAFETY

GCE ProControl® has been designed for use with all common technical gases up to 300bar cylinder pressure. All safety-related specifics of the oxygen and flammable gases, as well as high-pressure hazards, have been considered in product design. It has passed a full set of type tests conforming to ISO 2503. The product safety has been proven in long-term field tests with selected users making various applications.

### PRECISE ADJUSTMENT

Gas pressure and flow accuracy are the main parameters which the user requires from the pressure regulator. But GCE ProControl® users do not need to worry about that. They can just set the gas parameters for the application they are working with.

### ERGONOMIC DESIGN

9 of 10 users have confirmed they like to work with GCE ProControl®. When fitted to the cylinder valve the position of the pressure adjusting mechanism makes setting easy. Outlet shut-off valve in the right position gives the chance to switch off the gas flow without depressurising the regulator. This also increases the lifetime of the internal parts and saves cost with operation breakdowns and related services. Pressure gauges with three main unit high-contrast scales allow reading the set value in difficult light conditions. The Instruction for Use can be scanned from the QR code present on the product label during all its lifetime.

### SUITS TO APPLICATION

GCE ProControl® fits users of common technical gases with product variants specific for all markets, gases, and pressures available.

## FEATURES

- **High-performance** regulator following all common technical gas applications needs
- **Safety** focused design following ISO 2503
- **Robust** rubber gauge **protection** with back lid preventing damages and impurities
- Prolonged lifetime **saving costs** related to services, spares, and replacements
- Encapsulated regulating technology for **precise** parameters **stability**
- Easy handling for the operator by **ergonomic** arrangement
- Three scale pressure gauges acc. to ISO 5171 with high contrast pointer for **better** gas pressure **clarity**

## TECHNICAL DATA

Gas	O <sub>2</sub> , N <sub>2</sub> , H <sub>2</sub> , He	Ar, Ar/CO <sub>2</sub>	CO <sub>2</sub>	Acetylene	Propane
Body	Brass forged				
Bonnet	Zn/Al alloy Die Cast				
Stems, nuts and fittings	Brass				
Diaphragm	EPDM			NBR	
Seat sealing	PA			CR	
Inlet/ Outlet connection	Gas specific connection				
Maximal inlet pressure	200 or 300 bar		200 bar	25 bar	
Outlet pressure/ flow range	0-10 bar	0-16l/min 0-24l/min 0-30l/min	1,5 bar	4 bar	
	0-20 bar				
	0-30 bar				
	0-50 bar				
Temperature range	From -20°C to 60°C				
Weight	Approx. according to gas variant: 1,9 kg				
Pressure relief valve	Used in all variants				





