



FAG

6308-Z

Deep groove ball bearing

Deep groove ball bearing 63...-Z, single row, shield , steel sheet metal cage

Technical information



Your current product variant

Sealing	Z	Non-contact shield on one Side
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	90 mm	Outside diameter
B	23 mm	Width
C _r	45,500 N	Basic dynamic load rating, radial
C _{0r}	25,000 N	Basic static load rating, radial
C _{ur}	1,690 N	Fatigue load limit, radial
n _G	10,800 1/min	Limiting speed
n _{gr}	9,000 1/min	Reference speed
≈m	0.618 kg	Weight



Mounting dimensions

d a min	49 mm	Minimum diameter shaft shoulder
D a max	81 mm	Maximum diameter of housing shoulder
r a max	1.5 mm	Maximum fillet radius

Dimensions

r min	1.5 mm	Minimum chamfer dimension
D 1	74.64 mm	Shoulder diameter outer ring
D 2	76.5 mm	Caliber diameter outer ring
d 1	55.55 mm	Shoulder diameter inner ring

Temperature range

T min	-30 °C	Operating temperature min.
T max	120 °C	Operating temperature max.

Calculation factors

f 0	13	Calculation factor
-----	----	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Sealed on one side