



WESTCODE SEMICONDUCTORS

Technical
Publication
TN280C

Issue 1
April 1985

Converter Grade Capsule Thyristor Type N280C 735 amperes average: up to 1400 volts V_{RRM}

Ratings (Maximum values at 125°C T_j unless stated otherwise)

RATING	CONDITIONS	SYMBOL	
Average on-state current	Half sine wave $\left\{ \begin{array}{l} 55^{\circ}\text{C heatsink temperature} \\ \text{(double side cooled)} \\ 85^{\circ}\text{C heatsink temperature} \\ \text{(single side cooled)} \end{array} \right.$	$I_{T(AV)}$	735 A 290 A
R.M.S. on-state current	25°C heatsink temperature, double side cooled	$I_{T(RMS)}$	1470 A
Continuous on-state current	25°C heatsink temperature, double side cooled	I_T	1230 A
Peak one-cycle surge (non-repetitive) on state current	10ms duration, 60% V_{RRM} re-applied 10ms duration, $V_R \leq 10$ volts	$I_{TSM(1)}$ $I_{TSM(2)}$	7600 A 8360 A
Maximum permissible surge energy	10ms duration, $V_R \leq 10$ volts 3ms duration, $V_R \leq 10$ volts	$I^2t(2)$ I^2t	349000 A ² s 256000 A ² s
Peak forward gate current	Anode positive with respect to cathode	I_{FGM}	20 A
Peak forward gate voltage	Anode positive with respect to cathode	V_{FGM}	18 V
Peak reverse gate voltage		V_{RGM}	5 V
Average gate power		P_G	2 W
Peak gate power	100μs. pulse width	P_{GM}	100 W
Rate of rise of off-state voltage	To 80% V_{DRM} gate open-circuit	dv/dt	*200 V/μs
Rate of rise of on-state current (repetitive)	$\left\{ \begin{array}{l} \text{Gate drive 20 volts, 20 ohms with } t_r \leq 1\mu s. \\ \text{Anode voltage } \leq 80\% V_{DRM} \end{array} \right.$	$di/dt(1)$	500 A/μs
Rate of rise of on-state current (non-repetitive)		$di/dt(2)$	1000 A/μs
Operating temperature range		T_{hs}	-40 + 125°C
Storage temperature range		T_{stg}	-40 + 150°C

Characteristics (Maximum values at 125°C T_j unless stated otherwise)

CHARACTERISTIC	CONDITIONS	SYMBOL	
Peak on-state voltage	At 1550 A, I_{TM}	V_{TM}	1.78 V
Forward conduction threshold voltage		V_O	1.03 V
Forward conduction slope resistance		r	0.483 mΩ
Repetitive peak off-state current	At V_{DRM}	I_{DRM}	40 mA
Repetitive peak reverse current	At V_{RRM}	I_{RRM}	40 mA
Maximum gate current required to fire all devices	$\left\{ \begin{array}{l} V_A = 6 \text{ V, } I_A = 1 \text{ A at } 25^{\circ}\text{C } T_j \end{array} \right.$	I_{GT}	150 mA
Maximum gate voltage required to fire all devices		V_{GT}	3 V
Maximum holding current		I_H	500 mA
Maximum gate voltage which will not trigger any device		V_{GD}	0.25 V
Thermal resistance, junction to heatsink, for a device with a maximum forward volt drop characteristic	Double side cooled Single side cooled	$R_{th(j-hs)}$	0.05°C/W 0.1°C/W

VOLTAGE CODE		H02	H04	H06	H08	H10	H12	H14		
Repetitive peak voltages	V_{RRM} V_{DRM}	200	400	600	800	1000	1200	1400		
Non-repetitive peak off-state voltage	V_{DSM}									
Non-repetitive peak reverse blocking voltage	V_{RSM}	300	500	700	900	1100	1300	1500		

Ordering Information (Please quote device code as explained below – 8 digits)

N	2	8	0	C	● ● ●	Typical code: N280CH12 = 1200 V_{RRM} 1200 V_{DRM} , 200 V/μs dv/dt to 80% V_{DRM}
					Voltage code (see ratings)	







Figure 1 Dissipation and heatsink temperature v. current (Double side cooled)

Figure 2 Dissipation and heatsink temperature v. current (Single side cooled)




Figure 3 Junction to heatsink thermal impedance







Figure 4 Dissipation and heatsink temperature v. current (Double side cooled)

Figure 5 Dissipation and heatsink temperature v. current (Single side cooled)




Figure 6 Max. non-repetitive surge current at initial junction temperature 125°C.

(gate may temporarily lose control of firing angle)

Note: This rating must not be interpreted as an intermittent rating

TN280C




Figure 7 Gate characteristics at 25°C junction temperature




Figure 8 Gate triggering characteristics
Trigger points of all thyristors lie within the areas shown





Figure 9 Limit on-state characteristic



Dimensions in mm (inches)
Mounting force: 530–1000 Kgf
Weight: 90 grams

In the interest of product improvement, Westcode reserves the right to change specifications at any time without notice.

WESTCODE SEMICONDUCTORS LTD.

P.O. Box 57 Chippenham Wiltshire SN15 1JL England
Telephone Chippenham (0249) 654141 Telex 44751

HAWKER SIDDELEY
Westinghouse Brake and Signal Co. Ltd.