




LED R7s Slim 12X78 5W (34W) 390lm 830

Article number 80100040400

BAI LED R7s Slim 12x78mm 5W 3000K Clear 390lm (34W) 230V-240V 360° Linear LED-lamp Open luminaire is recommended

These LED R7s lamps with ultra-thin housing and all-round light are ideal as a replacement for the two-pinched halogen lamps. Originally this type of lamp is used in construction lamps, but they are also increasingly used for general lighting in homes or catering establishments. Ambient temperature range: -20°C to +45°C. An open luminaire is recommended for optimum performance in terms of light output and lifespan. Outdoor use only in suitable luminaires.



General ETIM properties

| | |
|---------------|--------------------|
| ETIM group | Lamps |
| ETIM class | LED-lamp/Multi-LED |
| Name | 80100040400 |
| Brand | Bailey |
| Productseries | LED Linear |
| Product type | R7s Slim |

ETIM specifications

| | |
|---|--------------------|
| Nominal voltage [V] | 220 - 240 |
| Nominal current [mA] | 22 - 22 |
| Power factor | 0.8 |
| Lamp power [W] | 5 - 5 |
| Voltage type | AC |
| Luminous flux [lm] | 390 - 390 |
| Rated luminous flux according to IEC 62612 [lm] | 390 |
| Lamp efficacy [lm/W] | 78 |
| Colour rendering index CRI | 80-89 |
| Lamp shape | Tube, double-ended |
| Filament lamp | No |
| Type of glass/cover | Clear |
| Colour of light according to EN 12464-1 | Warm white <3300 K |
| Socket | R7s |
| Colour | White |
| Colour temperature [K] | 3000 - 3000 |
| Colour housing | Grey |
| Beam angle [°] | 360 - 360 |
| Colour consistency (McAdam ellipse) | SDCM6 |
| Dimmable | No |
| Diameter [mm] | 12 |
| Length [mm] | 78 |
| Degree of protection (IP) | IP20 |
| Energy Efficiency Index (EEI) | 0.12 |
| Lamp designation | Other |
| Energy efficiency class | G |
| Min. number of switching cycles | 15000 |
| Weighted energy consumption in 1000 hours [kWh] | 5 |
| Average nominal lifespan [h] | 25000 |
| Remote operation possible | No |
| With remote control | No |
| Photobiological safety according to EN 62471 | Other |
| Compatible with Apple HomeKit | No |
| Compatible with Google Assistant | No |
| Compatible with Amazon Alexa | No |
| IFTTT support available | No |

Alternative articles



142580

LED R7s 28X78 DIM
6W (52W) 680lm 827
360D



142757

LED R7s Glass 14X78
4W (38W) 450lm 827



145771

LED R7s Glass 17x78
DIM 4.2W (40W) 470lm
827