

Specifications



Photo is representative

Eaton 239103

FAZ6-C16/2. Miniature circuit breaker (MCB),
16 A, 2p, characteristic: C, 6 kA

General specifications

PRODUCT NAME	Eaton Moeller series xEffect - FAZ6 MCB
CATALOG NUMBER	239103
MODEL CODE	FAZ6-C16/2
EAN	4015082391034
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	35.4 mm
PRODUCT WEIGHT	0.216 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

Delivery programme

NUMBER OF POLES (TOTAL)	2
NUMBER OF POLES (PROTECTED)	2
RELEASE CHARACTERISTIC	C
AMPERAGE RATING	16 A

Technical data - electrical

VOLTAGE TYPE	AC
VOLTAGE RATING (IEC/EN 60898-1)	415 V
VOLTAGE RATING (IEC/EN 60947-2)	400
RATED OPERATIONAL VOLTAGE (UE) - MAX	230 V
OPERATIONAL VOLTAGE (IEC/EN 60947-2) - MAX	400 V
OPERATIONAL VOLTAGE AT DC (EC/EN 60947-2) - MAX	60 V
RATED INSULATION VOLTAGE (UI)	440 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
FREQUENCY RATING - MIN	50 Hz
FREQUENCY RATING - MAX	60 Hz
RATED SWITCHING CAPACITY (IEC/EN 60947-2)	7.5 kA
RATED SERVICE SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)	6 kA
RATED SERVICE SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60947-2)	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60898) AT 230 V	6 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60898) AT 400 V	6 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2) AT 230 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2) AT 400 V	10 kA
OVERVOLTAGE CATEGORY	III
POLLUTION DEGREE	2

Technical data - mechanical

WIDTH IN NUMBER OF MODULAR SPACINGS	2
--	---

BUILT-IN DEPTH	70.5 mm
-----------------------	---------

DEGREE OF PROTECTION	IP20
-----------------------------	------

CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
---	-------------------

CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
---	--------------------

CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
--	-------------------

CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
--	--------------------

Design verification as per IEC/EN 61439 - technical data

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	16 A
--	------

EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT	4.7 W
---	-------

AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
--	--------

AMBIENT OPERATING TEMPERATURE - MAX	75 °C
--	-------

Design verification as per IEC/EN 61439

10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF	Is the panel builder's responsibility.

Additional information

CURRENT LIMITING CLASS	3
FEATURES	Additional equipment possible

INSULATING MATERIAL

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

APPLICATION NOTES	eaton-maximum-cable-lengths-for-eatons-protective-devices-brochure-br034006en-en-us.pdf
CATALOGUES	eaton-xeffect-faz-mcb-catalog-ca003028en-en-us.pdf eaton-xeffect-industrial-switchgear-range-catalog-ca003002en-en-us.pdf
CHARACTERISTIC CURVE	eaton-xeffect-faz6-mcb-characteristic-curve-002.jpg eaton-xeffect-faz6-mcb-characteristic-curve.jpg
DECLARATIONS OF CONFORMITY	eaton-mcb-declaration-of-conformity-eu250396en.pdf
DRAWINGS	eaton-xeffect-faz-mcb-dimensions-002.jpg eaton-xeffect-faz6-mcb-3d-drawing-002.jpg eaton-xeffect-faz6-mcb-3d-drawing-005.jpg
INSTALLATION INSTRUCTIONS	eaton-rccb-rcbo-g9-il019140zu.pdf
MCAD MODEL	faz_1pn_2p.dwg faz_1pn_2p.stp
PEP ECO-PASSPORT	EATO-00047-V01.01-EN
WIRING DIAGRAMS	eaton-xpole-mmc4-6-mcb-wiring-diagram-003.jpg

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

