

Universal cross rails, PanelSeT SFN, PanelSeT SF, PanelSeT SM, H40 W900mm, 1 row, set of 2

NSYSUCR4090

Main

Range	PanelSeT	
Accessory / separate part category	Mounting accessory	
Product or component type	Universal cross rail	
Application	Multi-purpose	
Nominal dimensions of the housing	- H: 900 mm	

Complementary

•		
Range compatibility	PanelSeT PanelSeT SF	
	PanelSeT PanelSeT SM	
	PanelSeT PanelSeT SFX	
	PanelSeT PanelSeT SMX	
Mounting location	Between cross rails	
Mounting support	Adaptation profile, on SM enclosures	
Device composition	fixing elements	
	2 cross rails	
	4 supports	
Quantity per set	Set of 1	
Material	Steel	
Surface finish	Galvanized	
Fixing mode	By screws	
Adjustment	Adjustable with a pitch of 25 mm	
Number of horizontal rows	1	
Maximum load	40 kg	
Height	Nominal: 900 mm	
	Useful: 807 mm	
Width	40 mm	
Depth	27 mm	
Thickness	1.5 mm	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	6.000 cm

Package 1 Length	81.500 cm
Package 1 Weight	1.632 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	10
Package 2 Height	29.000 cm
Package 2 Width	37.500 cm
Package 2 Length	120.000 cm
Package 2 Weight	16.320 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	12
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Packaging	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No