

MOLLY-W

~60° wide beam

TECHNICAL SPECIFICATIONS:

Dimensions Ø 69.8 mm Height 22.1 mm

Fastening

Colour clear

Box size 476 x 273 x 292 mm

Box weight 8.1 kg

Quantity in Box 198 pcs


ROHS compliant yes 1



MATERIAL SPECIFICATIONS:

ComponentTypeMaterialColourMOLLY-WSingle lensPMMAclear







PHOTOMETRIC DATA (MEASURED):




LED Vero SE 13
FWHM 62.0°
Efficiency 90 %
Peak intensity 0.860 cd/lm
LEDs/each optic 1

LEDs/each optic 1
Light colour White
Required components:

C16402_CLAMP-VEROSE-13-18







bridgelux.

LED Vero SE 18
FWHM 62.0°
Efficiency 90 %
Peak intensity 0.810 cd/lm

LEDs/each optic 1 Light colour White Required components:

C16402_CLAMP-VEROSE-13-18





CITIZEN


LED CLL03x/CLU03x

FWHM 58.0° Efficiency 90 % Peak intensity 0.930 cd/lm

LEDs/each optic 1 Light colour White Required components: C16791_CLAMP-Z45-A

TE: 2325807-3





CITIZEN

LED CLL03x/CLU03x

FWHM 61.0° Efficiency 89 % Peak intensity 0.850 cd/lm

LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 433 Typ L1



PHOTOMETRIC DATA (MEASURED):

CITIZEN


LED LCN-C02B (Tunable White)

White

FWHM 62.0° 89 % Efficiency Peak intensity 0.900 cd/lm LEDs/each optic 1

Required components: C13658_CLAMP-VERO13-18 Bender Wirth: 481 Typ L2






CREE &

Light colour

LED CMA1840 **FWHM** 64.0 + ° 91 % Efficiency Peak intensity 0.820 cd/lm

LEDs/each optic 1 Light colour White Required components: C14123_CLAMP-CXA15-18






CREE ÷

LED CMA2550 **FWHM** 63.0° Efficiency 89 % Peak intensity 0.770 cd/lm

LEDs/each optic 1 Light colour White Required components: C14036_CLAMP_CXA25-30






CREE ÷

LED CMA3090 **FWHM** 64.0° Efficiency 89 % 0.750 cd/lm Peak intensity

LEDs/each optic 1 White Light colour Required components:


C14036_CLAMP_CXA25-30







PHOTOMETRIC DATA (MEASURED):





PHOTOMETRIC DATA (MEASURED):




LED CDM-9 (Dim-To-Warm)

FWHM 61.0°
Efficiency 89 %
Peak intensity 0.860 cd/lm
LEDs/each optic 1
Light colour White

C13658_CLAMP-VERO13-18 Bender Wirth: 490 Typ L1





ELUMINUS

LED


Required components:

CTM-14 (Tunable White)

FWHM 62.0° Efficiency 88 % Peak intensity 0.830 cd/lm

LEDs/each optic 1
Light colour White
Required components:
C13584_CLAMP-VERO29
Bender Wirth: 442 Typ L3







ELUMINUS

LED CTM-22 (Tunable White)

FWHM 62.0° Efficiency 87 % Peak intensity 0.700 cd/lm

LEDs/each optic 1
Light colour White
Required components:
C13584_CLAMP-VERO29
Bender Wirth: 494 Typ L3





MNICHIA


LED NVCWJ024Z-V1MT: COB J-Type Tunable White

FWHM 60.0°
Efficiency 89 %
Peak intensity 0.900 cd/lm

LEDs/each optic 1 Light colour White Required components:

C13658_CLAMP-VERO13-18 Bender Wirth: 498 Typ L2







PHOTOMETRIC DATA (MEASURED):


OSRAM

LED PrevaLED Core G7 L15 H1

FWHM 57.0°
Efficiency 90 %
Peak intensity 0.950 cd/lm

LEDs/each optic 1 Light colour White Required components: C16685_CLAMP-PRV-A





PHILIPS

LED Fortimo SLM L13 CoB

FWHM 60.0° Efficiency 89 % Peak intensity 0.900 cd/lm

LEDs/each optic 1
Light colour White
Required components:

TE: 2213130-2 + OPTIC CLIP Z50 TYPE1 2213194-1



PHILIPS


LED Fortimo SLM L15 + SLM holder

FWHM 57.0° Efficiency 89 % Peak intensity 0.900 cd/lm

LEDs/each optic 1
Light colour White
Required components:

TE: OPTIC CLIP Z50 TYPE1 2213194-1





PHILIPS


LED Fortimo SLM L15 CoB

FWHM 60.0° Efficiency 88 % Peak intensity 0.900 cd/lm

LEDs/each optic 1
Light colour White
Required components:

TE: 2213130-2 + OPTIC CLIP Z50 TYPE1 2213194-1







PHOTOMETRIC DATA (MEASURED):


XICATO LED XTM - 19mm LES FWHM 60.0°

Efficiency 90 %
Peak intensity 0.880 cd/lm

LEDs/each optic 1 Light colour White Required components:

C16491_XTM-ADAPTER-50-A








PHOTOMETRIC DATA (SIMULATED):

bridgelux

LED VERO13 **FWHM** 55.0° 90 % Efficiency Peak intensity 1.100 cd/lm

LEDs/each optic 1 Light colour White Required components:

C13658_CLAMP-VERO13-18




CITIZEN

LED CLL02x/CLU02x (LES10)

FWHM 54.0° 89 % Efficiency Peak intensity 1.190 cd/lm

LEDs/each optic 1 White Light colour Required components: Bender Wirth: 434 Typ L1




CREE ÷

LED CXA/B 1816 & CXA/B 1820 & CXA 1850

FWHM 58.0° Efficiency 90 % Peak intensity 1.070 cd/lm

LEDs/each optic 1 Light colour White Required components: C14123_CLAMP-CXA15-18




CREE &

LED CXA/B 25xx **FWHM** 57.0° Efficiency

1.070 cd/lm Peak intensity

LEDs/each optic 1 White Light colour Required components:

C14036_CLAMP_CXA25-30



PHOTOMETRIC DATA (SIMULATED):


TRIDONIC

LED SLE G6 LES15 H D50

FWHM 52.0° Efficiency 84 % Peak intensity 1.140 cd/lm

LEDs/each optic 1 Light colour White Required components:

TE: OPTIC CLIP Z50 TYPE1 2213194-1




TRIDONIC

LED SLE G6 LES17 H

FWHM 55.0° Efficiency 87 % Peak intensity 1.100 cd/lm

LEDs/each optic 1
Light colour White
Required components:

TE: OPTIC CLIP Z50 TYPE1 2213194-1




TRIDONIC

LED SLE G6 LES19 H

FWHM 54.0° Efficiency 85 % Peak intensity 1.100 cd/lm

LEDs/each optic 1
Light colour White
Required components:

TE: OPTIC CLIP Z50 TYPE1 2213194-1





GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy