

95 11 200

Cable Shears with twin cutting edge



PATENTED



- for cutting copper and aluminium cables
- not suitable for steel wire and hard drawn copper conductors
- precision ground, hardened blades
- clean and smooth cut without crushing and deformation
- by dividing the cutting actions into initial cut (insulating sheath in the front cutting area) and final cut (conductor in the back cutting area), cables up to Ø 20 mm can be cut in one-hand operation
- less effort required due to favourable lever ratio and optimised cutting-edge geometry
- guard prevents operators' fingers being pinched
- adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened

The twin cutting edge allows a comfortable handle position in all cutting situations within the specified cutting capacity.

Article No.	95 11 200
EAN	4003773043928
Tool	burnished
Handles	plastic coated
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	20
Cutting capacity copper cable, multiple-stranded mm²	70
AWG	2/0
Length mm	200
Net weight g	283



Initial cut: using the front cutting edge to cut the insulating sheath on larger cable diameters leaves an ergonomic handle opening width.



Final cut: after cutting the sheath in the front profile the conductors in the rear part are cut. Initial cut in the front profile, final cut in the rear profile - to keep it as easy as possible.

technical change and errors excepted

