


FEATURES

- **Annealed Copper Conductor:** Provides superior electrical conductivity and durability
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and mechanical stress
- **Plain Conductor Type:** Ensures consistent performance and ease of installation
- **24/0.2 Core Strands:** Enhances flexibility for easy routing and installation
- **Temperature Range -15 °C to 70 °C:** Suitable for a wide range of operating conditions
- **Voltage Rating 500 V:** Supports high voltage applications safely
- **Outside Diameter 7.6 mm:** Compact size for space-constrained installations

RS PRO 0.75 mm² Flexible Cable, 100 m

RS Stock No: 606-134



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial environments. With a conductor made of annealed copper, it ensures excellent conductivity and durability. The cable is suitable for applications requiring flexibility and resilience, making it ideal for installations in confined spaces.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	Black
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	0.75 mm ²
Cable Length	100 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	3
Outside Diameter	7.6 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------