


## Features

- Metric threads
- High mechanical strength
- Ideal for use where good insulation and corrosion resistance is required
- Suitable for use in high voltage assemblies
- Moulded from ivory coloured Nylon 6,6

## RS PRO Machine Screws

RS Stock No.: 0326877



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*RS Pro machine screws are moulded from ivory coloured Nylon 6,6. This countersunk head machine screw features metric thread and high mechanical strength. The machine screw is ideal for use where good insulation and corrosion resistance is required. This screw is suitable for use in high voltage assemblies.*

## General Specifications

|            |             |
|------------|-------------|
| Head Shape | Countersunk |
| Drive Type | Slot        |

## Mechanical Specifications

|                    |           |
|--------------------|-----------|
| Metric or Imperial | Metric    |
| Material           | Nylon 6,6 |
| Finish             | Plain     |

## Product Table

| Thread Size (M) | RS Stock No. / Length (L) |         |         |         |         |         |         |         | Head Size    |               |     |
|-----------------|---------------------------|---------|---------|---------|---------|---------|---------|---------|--------------|---------------|-----|
|                 | 6                         | 8       | 10      | 12      | 16      | 20      | 25      | 30      | A (Head Ht.) | B (Head Dia.) | C   |
| M2 x 0.4        | 2326910                   |         | 2326903 |         | 2326906 |         | 2326907 |         | 1.2          | 3.8           | 0.5 |
| M2.5 x 0.45     | 2326901                   |         |         | 2326895 | 2326897 |         |         |         | 1.5          | 4.7           | 0.6 |
| M3 x 0.5        | 2326931                   | 0326877 | 2326914 |         | 2326919 | 2326921 | 2326924 | 2326926 | 1.65         | 5.5           | 1   |
| M3.5 x 0.6      |                           |         |         |         | 2326912 |         | 2326913 |         | 1.93         | 6.5           | 1   |
| M4 x 0.7        | 2326953                   | 0326878 |         | 2326941 | 2326943 | 2326946 | 2326948 |         | 2.7          | 8.4           | 1.3 |
| M5 x 0.8        |                           | 0326880 |         | 2326962 | 2326964 | 2326967 | 2326969 |         | 2.7          | 9             | 1.4 |
| M6 x 1.0        |                           | 2326989 |         |         | 2326982 | 2326984 | 2326985 |         | 3.3          | 11            | 1.8 |

Dimensions are in millimetres (mm)

## Approvals

Standards Met

DIN 963 / ISO2009

