



Switches > Toggle Switches



Contact Current Rating: **.4 A**
Configuration (Pole-Throw): **Double Pole - Double Throw**
Operating Function: **On On**
Number of Positions: **2**
Operating Voltage: **20 VDC**

Features

Product Type Features

Sealed Device	Yes
Toggle Style	Baton Long
Switch Type	Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	On On
Number of Positions	2

Electrical Characteristics

Contact Current Rating	.4 A
Operating Voltage	20 VAC

Body Features

Case Color	Red
Product Orientation	Vertical
Bushing Style	Threaded
Bushing Thread Size	1/4-40

Contact Features

Switch Contact Plating Material	Gold
---------------------------------	------

Termination Features



Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Product Mount Type	Panel & Printed Circuit Board
--------------------	-------------------------------

Housing Features

Process Sealed	No
----------------	----

Dimensions

Toggle Length	10.4 mm[.41 in]
---------------	-----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer











This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 <p>TE Part # 2267076-3 PMS8P1B09M2RE</p>	 <p>TE Part # 2267074-4 PMS9P1B05M2QE</p>	 <p>TE Part # 2267074-1 PMS9P1B05M2RE</p>	 <p>TE Part # 2267074-3 PMS9P1B05M2QE</p>
--	---	--	--

Customers Also Bought

 <p>TE Part #5052862013 RNF-100-3/64-4-STK</p>	 <p>TE Part #1-200833-1 SERIES" M " GUIDE PIN ST. STL.</p>	 <p>TE Part #282836-8 TERMI-BLOK PCB MOUNT 90 8P.</p>	 <p>TE Part #1-1437719-1 T01-0540-P03-MALE PLUG CONNECTOR-CRIMP</p>
 <p>TE Part #1-160304-0 250 FASTON,REC.,14-17AWG,BR</p>	 <p>TE Part #5499786-4 A/L UNIV HDR 20P RA LAT</p>	 <p>TE Part #2-1617118-1 J1MACD-26XMS = M39016/23-036M</p>	 <p>TE Part #1165384001 CGPT-9.5/4.8-X-FSP</p>
 <p>TE Part #5-160506-1 250 FASTON REC 20-16 AWG BR</p>	 <p>TE Part #1-87756-8 MOD IV RECP LP</p>		

Documents

Product Drawings

[TMD1T4B5M1QE](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2267077-3_A1.3d_igs.zip](#)



English

Customer View Model

[ENG_CVM_CVM_2267077-3_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267077-3_A1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Subminiature Switches](#)

English