

Shear Wrench XGT®

WT001G

40V Max

Model WT001G is a cordless shear wrench powered by 40Vmax XGT® Li-Ion battery.

Compatible bolt size: M16 (5/8"), M20 (3/4"), M22 (7/8"). Work amount: approx. 250 pcs of M22 Torque shear bolt with a 4.0Ah battery. Battery capacity warning lamp: LED blinks to notify user of decrease in battery capacity. Hook designed for use with Shoulder belt to carry the tool.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
No load speed	17 min ⁻¹
Max Fastening Torque Impact Drill	804 Nm
Sound Power Level (L _{WA})	90 dB(A)
Sound Pressure Level (L _{pA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	5,2 - 5,9 kg
Product Dimensions (L x W x H):	289 x 95 x 340 mm
Max. fastening torque Hard/Soft	- / 804 Nm
Product net weight	4,6 kg
Vibration Level, Screwdriving Without Impact	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Screwdriving Without Impact	1,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- Electric brake for maximum productivity and increased operator safety
- Anti-restart function minimises accidental start-up
- Battery capacity warning function automatically notifies the user about reduction in battery capacity with the decrease of illuminance
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing