




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Termination Method to Wire & Cable: **Crimp**

Connector System: **Wire-to-Board, Wire-to-Wire**

Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	9
Number of Rows	3

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

--	--



Multiple Contact Types	Without
Contact Layout	Matrix
Contact Type	Socket
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Material	Nylon
Centerline (Pitch)	6.35 mm[.25 in]

Dimensions

Row-to-Row Spacing	6.35 mm[.25 in]
	.03 – .09 in

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
Glow Wire Rating	GWT 750°C (Without Flame)
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-794761-8
09P UMNL CAP HSG,P/MT,V0,GRAY



TE Part # 1863003-1
09P UMNL PLUG HSG



TE Part # 1586846-1
06P UMNL PLUG HSG NATL, GW



TE Part # 1-480708-0
12P UMNL PLUG HSG NATL



TE Part # 770028-1
09P UMNLII IN-LINE CAP HSG KIT




TE Part # 794715-1
09P UMNL CAP HSG NATL,PAN MNT



TE Part # 2029314-1
09P UMNL PLUG HSG 150C-RED



TE Part # 1-480706-2
09P UMNL PLUG HSG RED



TE Part # 1-480707-2
09P UMNL CAP HSG RED



TE Part # 1-480704-0
06P UMNL PLUG HSG NATL



TE Part # 1586853-1
09P UMNL CAP HSG, GW



TE Part # 1-350782-9
09P UMNL V0 CAP HSG BLACK



TE Part # 794096-1
06P UMNL PLUG



TE Part # 794761-1
09P UMNL CAP HSG WHITE,P/MT,V0



TE Part # 1-794761-4
09P UMNL CAP HSG,P/MT,V0, YELLOW




TE Part # 1-794761-5
09P UMNL CAP HSG,P/MT,V0, GREEN



TE Part # 1-640406-0
05P UMNL VALVE CONN HSG



TE Part # 927231-3
HONHUS UMNL V0 9-P



TE Part # 1-794761-1
09P UMNL CAP HSG,P/MT,V0,BROWN



TE Part # 1-480707-1
09P UMNL CAP HSG BRN

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Contacts(208)



Connector Hardware(12)



Power Contacts(208)



Rectangular Power Connectors(651)



Standard Circular Connectors(1)

Customers Also Bought





TE Part #2-826656-0
20P AMPMODU II STIFT LEI




TE Part #2-322873-5
DG 22-16 HT ALUMEL R 6




TE Part #52266-4
TERMINAL R PG 4 3/8



TE Part #D369-P99-NP0
369 9 WAY PLUG, NO CONTACTS, PIN



TE Part #205202-2
20DF PIN CONTACT, PLATED




TE Part #966067-7
FER, WIRE, PL SLV, .75/18, L12, GREY, LP




TE Part #5-103956-4
4X5 MTE RCPT SR LATCH .100CL



TE Part #5207872-1
KIT SCREWLOCK FEMALE (METRIC)



TE Part #182794-000
TTMS-19.0-9



TE Part #826415-000
TTMS-12.7-9

Documents

Product Drawings
09P UMNL PLUG HSG NATL, GW
English

CAD Files
Customer View Model
ENG_CVM_CVM_1586844-1_B1.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1586844-1_B1.3d_stp.zip
English
Customer View Model
ENG_CVM_CVM_1586844-1_B1.3d_igs.zip
English
3D PDF
3D

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Agency Approvals

UL

English