



MUSTANG ESD - S1

Réf. : 45833



Suitable for :	Inside
Type :	Low shoe
Activity :	Electronic Industry, ESD / ATEX Zone
Upper :	Suede leather and breathable 3D type material
Lining :	AIR SYSTEM® red and black colours
Tongue :	Perforated microfibre
Ankle protection :	
Fastening :	Fabric straps and polyester flat laces red colour
Toe cap :	Ultra light and extra wide 200 joules Composite LIGHT SYSTEM®
Midsole :	
Insole :	Foam thermoformed, anatomical, absorbent, anti-bacterial, special ESD treatment
Sole :	Dual density PU outsole, HI-CI insulated, oil resistant FO, antistatic ESD
Sole pattern :	Multi-purpose, exclusive SOFT SYSTEM® concept, slip resistance SRC
Weight (Kg/pair) :	0.850
Colors :	Black and red upper and dual dark grey/light grey sole
Sizes :	35-48 (2-13)
Standard :	EN ISO 20345:2011 SRC / EN 61340-4-3:2001 - ATEX 1999/92/CE
CE certificate of conformity N° :	0075/020/161/03/18/0511 EXT 01/03/18
Special features :	Mixed model, available from size 35
Special features 2 :	Fabric loop at the heel for heasy and fast pull-on
Special features 3 :	Exceptional flexibility and lightness

SPECIAL FEATURES

-  200 joules light composite toecap
-  Metal free, non magnetic
-  Maximum foot ventilation
-  Electro Static Discharge Standard EN 61340-5-1

GENERAL FEATURES

	Antistatic properties (A)	YES	YES
	Heel energy absorption (E)	YES	YES
	Abrasion resistance	YES	YES
	Crampon sole	YES	YES
	Heat-insulated sole (HI)	YES	YES
	Cold-insulated sole (CI)	YES	YES
	200 joule extra-wide toecap	YES	YES
	Hyper-ventilated lining	YES	YES
	Perforation-resistance 1100 N (P)	YES	