

Product datasheet

Specifications



APC Smart-UPS Line Interactive
2200VA, Lithium-ion, Rack, 2U,
230V, 8x IEC C13 + 1x IEC C19,
SmartConnect+SmartSlot, AVR,
LCD

SMTL2200RMI2UC

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Uninterruptible power supply (UPS)
---------------------------	------------------------------------

Complementary

Communication port type	SmartConnect Ethernet port SmartSlot
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery type	Li-Ion (Lithium-Ion)
Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several v
Extended runtime	0
Battery recharge time	2 h
Number of battery replacement quantity	1
Battery design life	8...10 year(s)
Battery charger power	216 W rated
Replacement battery	APCRBC174-LI

General

Provided equipment	Rack mounting brackets Rack mounting support rails Screw Washer USB cable Ethernet patch cable
Number of power module	0
product web sub-family	Cloud-enabled monitoring
Redundant	No

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Physical

Number of rack unit	2U
Colour	Black with silver front bezel
Height	8.6 cm
Width	43.2 cm
Depth	68.3 cm
Product weight	33.3 kg
Mounting preference	Lower
Mounting mode	Rack-mounted
USB compatible	Yes

Input

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Input Connection Type	IEC 60320 C20
Input protection type	Circuit breaker
Input voltage limits	160...286 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	1980 W
Rated power in VA	2200 VA
output connection type	8 IEC 60320 C13 1 IEC 60320 C19
Crest factor	3 : 1
Maximum configurable power in VA	2200 VA
Maximum configurable power in W	1980 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	UK PSTI
------------------------	---------

Environmental

Acoustic level	55 dB
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C

Ambient air temperature for storage	-15...45 °C
Storage altitude	0.0000000000...7620.0000000000 m
IP degree of protection	IP20
Relative humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Communications & Management

Alarm	Audible and visible alarms
control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slots	1
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm

Surge Protection and Filtering

Surge energy rate	739 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	45.8 cm
Package 1 Width	60 cm
Package 1 Length	98 cm
Package 1 Weight	41.5 kg

Logistical informations

Country of origin	PH
-------------------	----

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	0637234b-27c7-4e32-ae29-543dd4803a99
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	No

Image of product / Alternate images

Alternative

