

C1046E040

trip unit MicroLogic 6.2 E for ComPacT NSX
100/160/250 circuit breakers, electronic, rating
40A, 4 poles 4d



Main

Range	ComPacT new generation
Range of product	ComPacT NSX100...250 new generation
Product or component type	Trip unit
Trip unit name	Micrologic 6.2 E
Trip unit technology	Electronic
Range compatibility	ComPacT new generation NSX100 ComPacT new generation NSX160 ComPacT new generation NSX250
Device application	Distribution
Poles description	4P
Protected poles description	3D + N/2 4D 3D + OSN 3D
Neutral position	Left
Trip unit protection functions	LSIG
Protection type	L : for overload protection (long time) S : for short time short-circuit protection I : for instantaneous short-circuit protection G : for ground fault protection
Trip unit rating	40 A at 40 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Circuit breaker mounting mode	Fixed

Complementary

Long-time pick-up adjustment type Ir (thermal protection)	Adjustable 9 settings
[Ir] long-time protection pick-up adjustment range	18...40 A
Long-time protection delay adjustment type tr	Adjustable
[tr] long-time protection delay adjustment range	15...400 S at 1.5 x Ir 0.35...11 S at 7.2 x Ir 0.5...16 s at 6 x Ir
Neutral protection settings	0.5 x Ir (3D + N/2) 1 x Ir (4D) 1.6 x Ir (3D + OSN) No protection (3D)
Thermal memory	20 minutes before and after tripping
Short-time protection pick-up adjustment type Isd	Adjustable 9 settings
[Isd] Short-time protection pick-up adjustment range	1.5...10 x Ir
Short-time protection delay adjustment type tsd	Adjustable
[tsd] Short-time protection delay adjustment range	0...0.4 S I ² t=off 0.1...0.4 s I ² t=on
Instantaneous protection pick-up adjustment type Ii	Adjustable
[Ii] instantaneous protection pick-up adjustment range	1.5...15 x In
Ground-fault protection pick-up adjustment type Ig	Adjustable

[I _g] ground-fault protection pick-up adjustment range	0.4...1 x I _n for I _n = 40 A 0.2...1 x I _n for I _n > 40 A I _g enable on/off
Ground-fault protection time delay adjustment type t _g	Adjustable
[t _g] ground-fault protection time delay adjustment range	0...0.4 s I ² t=off 0.1...0.4 s I ² t=on
Earth-leakage protection	Without
Zone selective interlocking ZSI	With
Local signalling	Flashing LED (green) for ready to operate LED 105 % I _r (red) for overload LED 90 % I _r (orange) for overload
Display type	LCD display
Type of measurement	Energy meter
Communication of data	Energy metering Protection and alarm settings Time-stamped histories and event tables Instantaneous and demand values Maintenance indicators Demand current and power Power quality Maximeters/minimeters
Electrical data recording	Maintenance indicators

Environment

Standards	EN/IEC 60947-2
Electrical shock protection class	Class II
Pollution degree	3 conforming to IEC 60947-1
IP degree of protection	IP40 conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	11.0 cm
Package 1 Length	15.0 cm
Package 1 Weight	668.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	11
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7.828 kg
Package 3 Height	150 cm

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------