

SACC-DSI-FS-5CON-L180/SH BU - Device connector rear mounting



1457940

<https://www.phoenixcontact.com/gb/products/1457940>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Socket, straight, M12-SPEEDCON, coding: A, Rear mounting, M16 x 1.5, Solder pins, this item is undergoing a smooth changeover, lead-free alternative in accordance with RoHS II without exception 6c (Pb < 0.1%) possible on request in advance

Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- All standard pin assignments and codings for signal, data, and power transmission with a uniform design-in design
- For high transmission reliability: optional shield connection to the housing by means of shield contact

Commercial data

Item number	1457940
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABQCAB
Product key	ABQEHB
Catalog page	Page 62 (PC-2011)
GTIN	4046356632706
Weight per piece (including packing)	14.53 g
Weight per piece (excluding packing)	13.561 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-FS-5CON-L180/SH BU - Device connector rear mounting



1457940

<https://www.phoenixcontact.com/gb/products/1457940>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Mounting

Mounting type	Rear mounting M16 x 1.5 With flat nut
Assembly note	With flat nut

Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	yes
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

Length of the solder pin	6 mm
	6 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Solder pins
Contact connection type	Socket

SACC-DSI-FS-5CON-L180/SH BU - Device connector rear mounting



1457940

<https://www.phoenixcontact.com/gb/products/1457940>

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101


SACC-DSI-FS-5CON-L180/SH BU - Device connector rear mounting

1457940

<https://www.phoenixcontact.com/gb/products/1457940>

Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

SACC-DSI-FS-5CON-L180/SH BU - Device connector rear mounting





1457940

<https://www.phoenixcontact.com/gb/products/1457940>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1457940>

<div> cULus Recognized Approval ID: E221474-20140616</div>				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	-	-

<div> UL Recognized Approval ID: E118976-20100522</div>				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	22	-

SACC-DSI-FS-5CON-L180/SH BU - Device connector rear mounting



1457940
<https://www.phoenixcontact.com/gb/products/1457940>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-FS-5CON-L180/SH BU - Device connector rear mounting



1457940

<https://www.phoenixcontact.com/gb/products/1457940>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	76dac4eb-6069-4f4e-ab55-0ac8f61e1991

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk