



Connectors > Terminal Blocks & Strips > Modular Terminal Blocks



Modular Terminal Block Product Type: **Screw Terminal Block**

Primary Product Color: **White**

Product Spacing: **12.7 mm [.5 in]**

Number of Positions: **1**

Centerline (Pitch): **12.7 mm [.5 in]**

Features

Product Type Features

Modular Terminal Block Product Type	Screw Terminal Block
-------------------------------------	----------------------

Configuration Features

Number of Circuits	1
Number of Positions	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	White
-----------------------	-------

Contact Features

Contact Current Rating (Max)	65 A
------------------------------	------

Termination Features

Termination Method to Wire & Cable	Tubular Clamp
------------------------------------	---------------

Housing Features

Centerline (Pitch)	12.7 mm[.5 in]
--------------------	----------------

Dimensions

Product Spacing	12.7 mm[.5 in]
Wire Size	18 – 6 AWG

Industry Standards

--	--



UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2016 (169) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1SNL906605R0000
BJC16-5



TE Part #1SNL606010R0000
C4/6



TE Part #1SNL900100R0000
EP5-6



TE Part #1SNL906603R0000
BJC16-3





TE Part #1SNL606150R0000
[C4/6.P](#)




TE Part #1SNK900001R0000
[BAM4](#)



TE Part #1SNL906602R0000
[BJCI6-2](#)



TE Part #1SNL610010R0000
[C10/10](#)



TE Part #1SNA231000R0700
[RC510](#)



TE Part #1SNA233000R0100
[RC610](#)

Documents

[Datasheets & Catalog Pages](#)
[BUCHANAN NEMA Terminal Blocks - Catalogue](#)
English