



Connectors > Rectangular Connectors > Standard Rectangular Connectors > STD Temp GRACE INERTIA Plug



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Mating Alignment: **With**

Mating Alignment Type: **Keyed**

Mating Retention: **With**

[All STD Temp GRACE INERTIA Plug \(25\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Connector & Keying Code	A
Primary Product Color	Natural



Contact Features

Contact Layout	Inline
Contact Base Material	Copper Alloy
Contact Type	Receptacle
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With
Mating Retention Type	Latch, Locking Latch
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon 66
Centerline (Pitch)	6.2 mm[.244 in]

Dimensions

Connector Height	14.15 mm[.556 in]
Connector Length	18.8 mm[.739 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	500
Packaging Method	Bag



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1746978-1
GRACE INERTIA 6.2mm PITCH CAP
3POS



TE Part # CAT-G7534-R2435
GRACE INERTIA Receptacle

Also in the Series | GRACE INERTIA 6.2



Connector Contacts(4)



Connector Hardware(1)



Power Contacts(4)



Rectangular Connector Housings(13)




Rectangular Power Connectors(13)



Standard Rectangular Connectors(13)

Customers Also Bought



TE Part #179974-1
250 PL EX REC. 18-14AWG PTBR



TE Part #1903414-1
GHC 9.0 3POS PLUG HSG




TE Part #170140-6
187 FASTON,FLAG,REC.,16-20 AWG, TPBR




TE Part #179975-1
250 PL EX REC. 15-10AWG PTBR




TE Part #41802
250 FASTON FLAG REC 18-12 AWG TPBR



TE Part #1746971-1
GRACE INERTIA CONNECTOR 6.2 MM PITCH REC



TE Part #179973-1
250 PL EX REC. 22-18AWG PTBR



TE Part #179970-2
PL EXII 250 REC HSG 1P NYLON RED



TE Part #1746973-1
GRACE INERTIA CONNECTOR 6.2 MM PITCH TAB



TE Part #41332
RING 18-14 AWG TPBR

Documents



Product Drawings

GRACE INERTIA 6.2mm PITCH PLUG 3POS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1871867-1_E3.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1871867-1_E3.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1871867-1_E3.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773883-5 GRACE INERTIA connector quick reference guide

English

Product Specifications

Application Specification

English