

Features

- Universal Input 90~264VAC
- Direct UK Fixed Plugtop Adapters
- UKCA & RoHS
- EN IEC 62368-1
- EMC Class B
- Single Output 7.5V DC
- OVP, OLP, SCP

RS PRO Desktop Power Supplies

RS Stock No.: 0625744



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO product is a high-quality and reliable 18W External AC/DC UK Plugtop Adapter Power Supply.

Designed for use in applications such as commercial, industrial and OEM electronics.

This product is supplied with a UK Fixed input connection and supports input voltages of 90~264V AC 50~60Hz.

Certified to UKCA, RoHS and compliant with EN IEC 62368-1.

Trusted in both development and production, this product serves the AV, computing, and ITE sectors.

General Specifications

Input Connector	UK Fixed
Output Connection Type	Jack connector 12 + 0.5mm
Number of Outputs	1
Energy Efficiency Level	VI
Mounting Style	Desktop
MTBF	224.6Khrs min.
Cable Length	1.5m
Medical Approved	Yes

Electrical Specifications

Input Specifications	
Rated Input Voltage	100~240VAC
Full Input Voltage Range	90~264V AC
Rated Frequency	50/60Hz
Full Frequency Range	50/60Hz
Efficiency	84%
Input Current (RMS Max.)	0.6A/115VAC
Inrush Current	Start 50A/200us at 230VAC 50Hz
Leakage Current (max.)	<0.25mA/230VAC

Output Specifications	
Ripple & Noise (max.)	75mVp-p
Voltage Tolerance	±5.0%
Hold Up Time (Typ.)	1.0s,60ms,20ms/230VAC(at full load)
Operating Humidity	20 ~ 95%RH Non-condensing
Storage Humidity	-40 ~ +85°C,10 ~ 95%RH Non-condensing
Operating Temperature Range	-20 ~ +60°C (Please refer to "Derating Curve" section)
Storage Temperature Range	-20 ~ +60°C

Mechanical Specifications

Housing Material	Fully Enclosed Plastic Case
Overall Dimensions	70 x 53 x 33 mm
Overall Length	70mm
Overall Depth	53mm
Overall Width	33mm

Protection Category


Over Voltage Protection	120~180% Shut down o/p voltage, re-power on to recover.
Over Load Protection	105~150% Hiccup mode, recovers automatically after fault condition is removed
Short Circuit Protection	Yes, Shut down o/p voltage, re-power on to recover.

Approvals



Safety Standard	EN IEC 62368-1
-----------------	----------------

Feature Curves


1. Derating Curve



2. Static Characteristics



Standard Model : D1J

D1J	Pin Assignment
 	<p>Pin Assignment:</p> 