

TeSys K contactor - 3P - AC-3 <= 440 V 9 A - 1 NO aux. - 24 V AC coil

Local distributor code:

20744265 LC1K0910B7

EAN Code: 3389110363623

Main

Main		
Range	TeSys	
Product or component type	Contactor	
Device short name	LC1K	
Device application	Control	
Contactor application	Motor control Resistive load	
Complementary		
Utilisation category	AC-3	
	AC-3e	
	AC-1	
	AC-4	

	Signalling circuit: <= 690 V AC <= 400 Hz
[le] rated operational current	9 A (at <60 °C) at <= 440 V AC AC-3 for po

power pole contact composition

[Ue] rated operational voltage

Poles description

[le] rated operational current

9 A (at <60 °C) at <= 440 V AC AC-3 for power circuit

9 A (at <60 °C) at <= 440 V AC AC-3 e for power circuit

20 A (at <60 °C) at <= 690 V AC AC-1 for power circuit

Control circuit type

AC at 50/60 Hz

[Uc] control circuit voltage	24 V AC 50/60 Hz
Motor power kW	2.2 kW at 220230 V AC 50/60 Hz AC-3 4 kW at 380415 V AC 50/60 Hz AC-3 4 kW at 440/690 V AC 50/60 Hz AC-3

3P

4 kW at 440/690 V AC 50/60 Hz AC-3 2.2 kW at 220...230 V AC 50/60 Hz AC-3e 4 kW at 380...415 V AC 50/60 Hz AC-3e 4 kW at 440/690 V AC 50/60 Hz AC-3e 2.2 kW at 220...230 V AC 50/60 Hz AC-4

Power circuit: <= 690 V AC <= 400 Hz

4 kW at 380415 V AC 50/60 Hz AC-4 4 kW at 440/690 V AC 50/60 Hz AC-4	
Auxiliary contact composition	1 NO
[Uimp] rated impulse withstand voltage	8 kV
overveltage estageny	III.

·	
overvoltage category	III
[Ith] conventional free air thermal current	20 A (at 60 °C) for power circuit 10 A (at 50 °C) for signalling circuit

Irms rated making capacity

110 A AC for power circuit conforming to IEC 60947

110 A AC for signalling circuit conforming to IEC 60947

Rated breaking capacity	110 A at 220230 V conforming to IEC 60947 110 A at 380400 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947	
	80 A at 500 V conforming to IEC 60947 70 A at 660690 V conforming to IEC 60947	
[lcw] rated short-time withstand current	90 A 50 °C - 1 s for power circuit 85 A 50 °C - 5 s for power circuit	
	80 A 50 °C - 10 s for power circuit 60 A 50 °C - 30 s for power circuit	
	45 A 50 °C - 1 min for power circuit	
	40 A 50 °C - 3 min for power circuit 20 A 50 °C - >= 15 min for power circuit	
	80 A - 1 s for signalling circuit	
	90 A - 500 ms for signalling circuit 110 A - 100 ms for signalling circuit	
Associated fuse rating	25 A gG at <= 440 V for power circuit	
	25 A aM for power circuit	
	10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660	
Average impedance	3 mOhm - Ith 20 A 50 Hz for power circuit	
Insulation resistance	> 10 MOhm for signalling circuit	
Inrush power in VA	30 VA (at 20 °C)	
Hold-in power consumption in VA	4.5 VA (at 20 °C)	
Heat dissipation	1.3 W	
Control circuit voltage limits	Operational: 0.81.15 Uc (at <50 °C) Drop-out: >= 0.20 Uc (at <50 °C)	
Connections - terminals	Screw clamp terminals 1 cable(s) 1.54 mm²solid Screw clamp terminals 1 cable(s) 0.754 mm²flexible without cable end Screw clamp terminals 1 cable(s) 0.342.5 mm²flexible with cable end	
	Screw clamp terminals 2 cable(s) 1.54 mm²solid Screw clamp terminals 2 cable(s) 0.754 mm²flexible without cable end Screw clamp terminals 2 cable(s) 0.341.5 mm²flexible with cable end	
Maximum operating rate	3600 cyc/h	
Auxiliary contacts type	type instantaneous 1 NO	
Signalling circuit frequency	<= 400 Hz	
Minimum switching current	5 mA for signalling circuit	
Minimum switching voltage	17 V for signalling circuit	
Operating time	1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing	
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1	
Non overlap distance	0.5 mm	
Mechanical durability	10 Mcycles	
Electrical durability	1.3 Mcycles 9 A AC-3 at Ue <= 440 V	
	1.3 Mcycles 9 A AC-3e at Ue <= 440 V 0.16 Mcycles 20 A AC-1 at Ue <= 690 V 0.02 Mcycles 54 A AC-4 at Ue <= 440 V	
Mechanical robustness	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5300 Hz conforming to IEC 60068-2-6	
Height	58 mm	

Width	45 mm
Depth	57 mm

Environment

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 IEC 60335-1:Clause 30.2 IEC 60335-2-40:Annex JJ UL 60335-2-40:Annex JJ
Product certifications	CB Scheme CCC UL CSA EAC CE UKCA
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Operating altitude	2000 m without derating
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

Packing Units

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.600 cm
Package 1 Width	4.800 cm
Package 1 Length	6.200 cm
Package 1 Weight	178.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.253 kg
Unit Type of Package 3	P06
Number of Units in Package 3	800
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	159.435 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	54
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
China RoHS Regulation	China RoHS declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No