

# KSA630DTC40

Tee, Canalis KSA630, aluminium , 500/630A, fixed dimensions (A/B/C 290mm), 3L+N+PE, white RAL9001



## Main

Range of product	Canalis
Product name	KS
Device short name	KSA
Offer type	Advanced
Product or component type	Tee
Busbar description	Standard
Product compatibility	Canalis KSA busbar trunking 500...1000 A
Device application	Change direction
Conductors material	Aluminium
Busbar trunking polarity	3L + N + PE
[Ie] rated operational current	630 A at 35 °C
IP degree of protection	IP55 conforming to IEC 60529
[Ue] rated operational voltage	230...690 V
Network frequency	50/60 Hz
Operating angle	90 °
Direction change type	Edgewise to perpendicular - neutral to up
Colour	White (RAL 9001)
Dimension type	Made to measure

## Complementary

Length	290 Mm for side A 290 Mm for side B 290 mm for side C
Width	113 mm
Height	146 mm
Net weight	10 kg
Mounting location	On trunking
Mounting position	Any position
Electrical connection	Lubricated sliding contact
Mounting mode	By screws
Standards	IEC 61439-1 IEC 61439-6

## Environment

IK degree of protection	IK08 conforming to IEC 62262
-------------------------	------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins