


**06700050**

RCK 70 - Self centring

**2D Technical Drawing**

**Dynamic 3D View**
**Technical Specifications**

Part number (CODE)	06700050
Ød (DD) mm	50
ØD (D) mm	80
L1 (L1) mm	30
L2 (L2) mm	36
L3 (L3) mm	47
L (L) mm	55
Maximum torque Mt (MT) Nm	2580
Clamping pressure - Shaft (CPS) N/mm <sup>2</sup>	218
Clamping pressure - Hub (CPH) N/mm <sup>2</sup>	135
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	6
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M8x30
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	41
Extraction thread - Type (ETT)	M8
Extraction thread - Num. (ETN)	3
Weight (WEIGHT) kg	1.00