


**P-series**  
**PRV 4 BL 35X7.5 RT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Save space by connecting with these multi-tier terminals with PUSH IN connection technology.

The product line includes the four-channel, eight-channel and also the innovative sixteen-channel feed-through terminal blocks. The four-channel and eight-channel terminals are also available as potential distribution terminals.

The benefits:

- More than 1700 signals per metre can be distributed with the 16-channel terminal block.
- Red and white actuators make it easier to assign wires to their terminal points.
- The PUSH IN connections make wiring quick and convenient.

#### General ordering data

Order No.	<a href="#">1267900000</a>
Type	PRV 4 BL 35X7.5 RT
Version	P-series, Patch distributor, Rated cross-section: 1.5 mm <sup>2</sup> , Number of levels: 4, Number of connections: 16, Colour: Blue, Colour of operational elements: Red, TS 35 x 7.5
GTIN (EAN)	4032248112807
Qty.	20 pc(s).

**P-series**  
**PRV 4 BL 35X7.5 RT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Length	70 mm	Width	9.2 mm
Height	47 mm	Net weight	21.31 g

**Temperatures**

Operating temperature	-25 °C...+70 °C	Storage temperature	-25 °C...+70 °C
Temperature range, installation, min.	-10 °C	Temperature range, installation, max.	40 °C

**CSA ratings data**

Certificate No. (CSA)	200039-2406089	Voltage size B (CSA)	300 V
Voltage size D (CSA)	300 V	Current size B (CSA)	10 A
Current size D (CSA)	10 A	Wire cross section max. (CSA)	16 AWG
Wire cross section min. (CSA)	26 AWG		

**Clampable wires (rated connection)**

Type of connection	PUSH IN	Stripping length	10 mm
Blade size	0.6 x 3.5 mm	Connection direction	Inclined / angled
Number of connections	16	Clamping range, rated connection, min.	0.2 mm <sup>2</sup>
Clamping range, rated connection, max.	1.5 mm <sup>2</sup>	Wire connection cross section, solid core, max. rated connection	0.2 mm <sup>2</sup>
Wire connection cross section, solid core max. rated connection	1.5 mm <sup>2</sup>	Wire connection cross section, stranded, rated connection, min.	0.2 mm <sup>2</sup>
Wire connection cross section, stranded, rated connection, max.	1.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	1.5 mm <sup>2</sup>
Wire connection cross-section, finely stranded, min.	0.2 mm <sup>2</sup>	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	0.2 mm <sup>2</sup>
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	1.5 mm <sup>2</sup>	Cross-section for connected conductor, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, min.	0.2 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, max.	1.5 mm <sup>2</sup>	Wire connection cross section AWG, min.	AWG 24
Wire connection cross section AWG, max.	AWG 16		

**Rated data**

Rated cross-section	1.5 mm <sup>2</sup>	Rated voltage	250 V
Rated impulse withstand voltage	4 kV	Rated current	10 A
Current at maximum wires	13 A	Pollution severity	3
Surge voltage category	III		

**UL ratings data**

Certificate No. (cURus)	E60693VOL1SEC99	Current size B (cURus)	10 A
Current size D (cURus)	10 A	Voltage size B (cURus)	300 V
Voltage size D (cURus)	300 V	Wire cross section max. (cURus)	16 AWG

**P-series  
PRV 4 BL 35X7.5 RT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Material data**

Material	Polycarbonate	Colour	Blue
Material of operational elements	PBT	Colour of operational elements	Red
UL 94 flammability rating	V-0		

**System specifications**

Product family	P-series	Type of connection	PUSH IN
Connection direction	Inclined / angled	Number of levels	4
Number of connections	16	No. of clamping points per level	4
Number of potentials per level	1	Mounting rail	TS 35 x 7.5
End cover plate required	Yes		

**Classifications**

eClass 6.0	27-14-11-20	eClass 7.0	27-14-11-20
------------	-------------	------------	-------------

**Product information**

Descriptive text ordering data	RT = red actuators
--------------------------------	--------------------

**Approvals**

Approvals



**Data sheet...**

**P-series**  
**PRV 4 BL 35X7.5 RT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

