



Passive Components > Resistors > Through-Hole Resistors



Resistance Value: 1K Ω
Resistor Type: Precision Resistor
Element Type: Wire Wound
Power Rating: .25 W
Resistance Class: 1k Ω – 1M Ω

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	300 V
Resistance Value	1K Ω
Power Rating	.25 W
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	9.53 x 4.75 mm
------------------------------	----------------



Usage Conditions

Operating Temperature Range	-55 – 145 °C
Temperature Coefficient	±5 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

UPW25B1K0V

1K ohm, Through-Hole Precision Resistor, Wire Wound, .25 W, .1 %, ±5 ppm/°C, Axial-Leaded, Copper Termination, 9.53 x 4.75 mm, Neohm UPW



TE Part # 1-1624323-0
UPW50 0.1% 5PPM 250R



TE Part # 1624323-6
UPW50 0.1% 5PPM 1K0



TE Part # 1624322-1
UPW25 0.1% 5PPM 100K



TE Part # 1-1624323-4
UPW50 0.1% 5PPM 500R



TE Part # 1624322-6
UPW25 0.1% 5PPM 250R

Also in the Series | [Neohm UPW](#)



[Through-Hole Resistors\(31\)](#)

Customers Also Bought



TE Part #5-1622820-9
3520 68R 5%




TE Part #3-1676913-2
YR1 0.1% 215K



TE Part #2-1625886-4
1W SM M/OX 5% 560R



TE Part #2-1419130-4
TSC-112L3H,000



TE Part #6-1879665-6
H8 59K 0.1% 15PPM



TE Part #1622591-1
LR1 1% 91K



TE Part #7-1676913-5
YR1 0.1% 2K67

TE Part #2-1768000-4
LBC-13029



TE Part #3-1991136-0
[GROMMET STRIP SIZE 4 NATURAL](#)

TE Part #5070012016
[RNF-100-3/64-X-STK](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1624322-5_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1624322-5_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1624322-5_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Ultra Precision Wire-Wound Resistors - Type UPW Series - Tyco Electronics Passives](#)

English