



SITOR fuse holder 22x 127 63 A 1500 V AC/1000 V DC 3-pole

Model	
product brand name	SITOR
product designation	SITOR fuse switch disconnecter
design of the actuating element	swivel knob
General technical data	
number of poles	3
size of fuse link	22x127
utilization category	AC20B/DC20B
size of the fuse link	22x127 mm
operating voltage	
• at AC rated value maximum	1 500 V
• at DC rated value maximum	1 000 V
Protection class	
protection class IP on the front	IP20
Main circuit	
operational current rated value	63 A
Suitability	
suitability for use main switch	No
suitability for use switch disconnecter	No
suitability for use EMERGENCY OFF switch	No
suitability for use safety switch	No
Product function	
product function fuse monitoring	No
Short circuit	
conditional short-circuit current (I _q) rated value	50 kA
Connections	
connectable conductor cross-section solid	
• minimum	1 mm ²
• maximum	50 mm ²
type of electrical connection for main current circuit	screw-type terminals
Mechanical Design	
height	200 mm
depth	102 mm
fastening method	
• floor mounting	Yes
• rail mounting	No
net weight	1 488 g
Approvals Certificates	
General Product Approval	other



[Confirmation](#)



[Confirmation](#)

[Miscellaneous](#)

Environment

[Environmental Conformations](#)

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC2393-0MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NC2393-0MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2393-0MK


CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





last modified:

4/20/2023 

