

#### **Datasheet**

RS Pro Flush Indicator, 8mm Mounting Hole Size, Hyper Bright Green LED, Faston, Solder Lug Termination, 24 V dc

RS Stock No: 913-8716



## **Product Details**

RS Pro flush indicator with 8 mm mounting hole, features hyper bright green LEDs for panel mount applications. With an IP67 rating, it is suitable for most environments including outdoor applications. This indicator accommodates a lamp size of 5 mm and offers extended short body solder lug/faston termination. It has a voltage rating of 24 V dc. The indicator has a wide operating temperature range of -40 to +85°C, further increasing the potential applications they may be used for. The 5 mm LED requires an 8 mm panel cut-out and is supplied with a fixing nut and spring washer. It offers a wide selection of voltage ratings, bezel finishes and bezel styles.

## **Features and Benefits**

- 8 mm panel mounting LED indicator
- Coloured diffused epoxy lens or water clear super bright LEDs
- · Prominent, recessed, chamfer and flush bezel styles
- Sealed to IP67
- Operating temperature range: -40 to +85°C






## **Specifications:**

Bezel Colour	Bright Chrome
Bezel Style	Flush
Current Rating	20 mA
Intensity	300 mcd
IP Rating	IP67
Lamp Size	5 mm
Lamp Type	LED
Length	22.6 mm
Light Output Colour	Green
Mounting Hole Size	8 mm
Termination Type	Extended Short Body Solder Lug/Fastons
Type	Panel Mount
Voltage Rating	24 V dc
Temperature Rating	-40 to +85°C
Type of Illumination	Fixed Light
LED Colour	Hyper Bright Green



TECHNICAL SPECIFICATIONS					
Voltage	Operating Voltage	Operating Current			
	(Min to Max)	(Typical All Types)			
02 (No Resistor)	1.8 to 3.3VDC	20mA max*			
6VDC	5.4 to 6.6VDC	20mA			
12VDC	10.8 to 13.2VDC	20mA			
24VDC	21.6 to 26.4VDC	20mA			
28VDC	25.2 to 30.8VDC	20mA			
110VAC	99 to 121VAC	6mA			
220VAC	207 to 253VAC	3mA			

**ENGLISH** 



Standard LED Intensity	Prominent and Recessed	Flush	Forward Voltage
HE Red	80mcd	8mcd	2.0V
Green	60mcd	6mcd	2.2V
Yellow	50mcd	6mcd	2.1V
Blue	1600mcd	50mcd	3.3V
White	1600mcd	500mcd	3.3V
Orange	60mcd	110mcd	2.2V
Bi-color (Typical) (Red/Green)	14/30mcd	15/10mcd	2.0V/2.2V
Tri-color (Typical) (Red/Green/Yellow)	60/15/13mcd	15/10/6mcd	2.0V/2.2V/2.1V
Bi-color - The col	or is changed by reversing the p	olarity of the supply volt	age.
Tri color The indicator	beered and groon I EDs when I	acth connected valley	is produced

Tri-color - The indicator has red and green LEDs, when both connected yellow is produced

Super Bright LED	Prominent and Recessed	Flush	Forward Voltage
HE Red	5,000mcd	1,300mcd	2.2V
Green	10,000mcd	1,200mcd	3.3V
Yellow	4,000mcd	350mcd	2.0V
Blue	2,200mcd	280mcd	3.3V
White	2,500mcd	950mcd	3.3V
Orange	4,000mcd	500mcd	2.2V

Hyper Bright LED	Prominent and Recessed	Flush	Forward Voltage
HE Red	6,000mcd	980mcd	2.2V
Green	1,900mcd	300mcd	3.3V
Yellow	1,600mcd	250mcd	2.0V
Orange	2,400mcd	110mcd	2.2V

Luminous intensity will be reduced with lower operating current. Note: The operating voltage must not be exceeded by more that 10% as this will result in reduced life expectancy.

The company reserves the right to change specifications without notice.

\* Customer to supply resistor for desired operating current.

Luminous intensity is measured at 20mA on a discrete LED unless otherwise stated.

Luminous intensities and color shades of white LEDs may vary within a batch.

LED characteristics are dependent upon environmental conditions. Therefore published data should be considered nominal.

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



## **ENGLISH**

# Technical Drawings FLUSH BEZEL

